

HDC HP 250 R KIT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

General ordering data

Version	HDC insert, Female, Male, Installation size: 250
Order No.	2786460000
Type	HDC HP 250 R KIT
GTIN (EAN)	4064675064008
Qty.	1 items

HDC HP 250 R KIT

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	62.5 mm	Length (inches)	2.4606 inch
Net weight	218.11 g		

Temperatures

Limit temperature	-50 °C ... 120 °C
-------------------	-------------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Installation size	250	UL 94 flammability rating	V-0
Colour	black	Type	Female, Male
Basic material	Copper alloy	Series	HighPower
Free from halogens	false	BG	250

Version

Installation size	250	Basic material	Copper alloy
BG	250		

Important note

Product information	Depending on the intended operation, internally generated voltages can superimpose the working voltage and contain corresponding peaks. It is imperative to ensure that these peak voltages do not exceed the rated voltage. For applications outside of this specification, please contact us. The rated voltage of 3.0 kV must be reduced by 20% at operating temperatures above 110°C.
---------------------	---

Classifications

ETIM 8.0	EC002943	ETIM 9.0	EC002943
ETIM 10.0	EC002943	ECLASS 14.0	27-44-02-92
ECLASS 15.0	27-44-02-92		

HDC HP 250 R KIT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

