

**IE-ANT-WL-DB-MIMO-DO-RPSMAM**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Antennas and antenna accessories (coax cables and mounts)

- State-of-the-art antennas
- Industry proven
- Robust design (up to IP67 protection)
- For outdoor and indoor use
- Latest technology support
- Up to Wi-Fi 6 and Wi-Fi 6E (2.4 GHz, 5 GHz, 6 GHz)
- Up to 5G (NR) support (700 MHz - 3.8 GHz)
- Also support for other technologies (e.g. Bluetooth, GNSS, etc.)
- Appropriate coax cables at different lengths
- Suitable pole and wall mounts

**General ordering data**

Version	Omni-directional antenna, Wi-Fi antenna, Up to Wi-Fi 6 & 6E (IEEE802.11ax), Linear, Vertical, 2x RP-SMA male, IP67, Impedance: 50 Ω
Order No.	<a href="#">2788070000</a>
Type	IE-ANT-WL-DB-MIMO-DO-RPSMAM
GTIN (EAN)	4064675066330
Qty.	1 items

## IE-ANT-WL-DB-MIMO-DO-RPSMAM

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Height	67 mm	Height (inches)	2.6378 inch
Diameter	137 mm	Net weight	467.95 g

### Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...80 °C
---------------------	----------------	-----------------------	----------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	e4cad7fc-a55e-4d5c-8f05-417a6385e9b6

### Enclosure material

Colour	white	Material for base plate	UV- stable rugged thermoplastics
--------	-------	-------------------------	----------------------------------

### Included in delivery

Included in delivery	1 x antenna
----------------------	-------------

### Mechanical and material properties of cable

Cable length	1 m	Min. bending radius, repetitive	25 mm
--------------	-----	---------------------------------	-------

### Technical data

Type of connection	2x RP-SMA male	Amount of antenna elements (MIMO)	2
Impedance	50 Ω	Standing wave ratio	< 2.0 typical, 2.5 max.
Composite power max.	25 W	Frequency range	2.3-2.8 GHz, 4.9-7.125 GHz
Antenna gain	1.5 dBi, 0.5 dBi	Polarisation	Linear, Vertical

### Environmental conditions

Operating temperature, max.	80 °C	Operating temperature, min.	-40 °C
Storage temperature, max.	80 °C	Storage temperature, min.	-40 °C

### Classifications

ETIM 8.0	EC001698	ETIM 9.0	EC001698
ETIM 10.0	EC001698	ECLASS 14.0	19-07-01-05
ECLASS 15.0	19-07-01-05		