

## IE-ANT-WL-DB-SISO-LO-NF

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Antennas and antenna accessories (coax cables and mounts)

- State-of-the-art antennas
- Industry proven
- Robust design (up to IP67 protection)
- For outdoor and indoor use
- Latest technology support
- Up to Wi-Fi 6 and Wi-Fi 6E (2.4 GHz, 5 GHz, 6 GHz)
- Up to 5G (NR) support (700 MHz - 3.8 GHz)
- Also support for other technologies (e.g. Bluetooth, GNSS, etc.)
- Appropriate coax cables at different lengths
- Suitable pole and wall mounts

### General ordering data

Version	Omni-directional antenna, Wi-Fi antenna, Up to Wi-Fi 6 & 6E (IEEE802.11ax), Vertical, N female, IP67, Impedance: 50 Ω
Order No.	<a href="#">2788110000</a>
Type	IE-ANT-WL-DB-SISO-LO-NF
GTIN (EAN)	4064675066378
Qty.	1 items

## IE-ANT-WL-DB-SISO-LO-NF

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Height	45.7 mm	Height (inches)	1.7992 inch
Diameter	36.2 mm	Net weight	138.29 g

### Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
---------------------	----------------	-----------------------	----------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	e4cad7fc-a55e-4d5c-8f05-417a6385e9b6

### Enclosure material

Colour	black
--------	-------

### Included in delivery

Included in delivery	1 x antenna
----------------------	-------------

### Technical data

Type of connection	N female	Impedance	50 Ω
Standing wave ratio	<2.0 typical, 3.5 max.	Composite power max.	100 W
Frequency range	2.4-2.5 GHz, 4.9-6.425 GHz	Antenna gain	3 dBi, 4 dBi
Polarisation	Vertical		

### Environmental conditions

Operating temperature, max.	85 °C	Operating temperature, min.	-40 °C
Storage temperature, max.	85 °C	Storage temperature, min.	-40 °C

### Classifications

ETIM 8.0	EC001698	ETIM 9.0	EC001698
ETIM 10.0	EC001698	ECLASS 14.0	19-07-01-05
ECLASS 15.0	19-07-01-05		