

IE-PCB-SPM-P-180-SMD


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



SPElink®



Single Pair Ethernet PCB sockets

Single pair Ethernet is a technology that only requires one pair of wires to transmit data and power.

The resulting benefits will make SPE the preferred network at the field level and beyond.

Advantages of Single Pair Ethernet:

- Consistent: Single Pair Ethernet enables uniform Ethernet-based communication from the sensor to the cloud
- Future-proof: key technology for Industry 4.0 and IIoT
- Flexible: ranges of up to 1000 m and transmission properties of up to 1 Gbps enable use across applications
- Innovative: lighter, less space required, and reduced installation effort

General ordering data

Version	Built-in plugs, M8 PCB insert, Solder connection, IP67 with housing, SMD solder connection, 180°, Number of poles: 2, Tape
Order No.	2795110000
Type	IE-PCB-SPM-P-180-SMD
GTIN (EAN)	4064675119166
Qty.	100 items
Packaging	Tape

IE-PCB-SPM-P-180-SMD

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	14.5 mm	Depth (inches)	0.5709 inch
Height	22.1 mm	Height (inches)	0.8701 inch
Width	10.1 mm	Width (inches)	0.3976 inch
Net weight	5.14 g		

Temperatures

Storage temperature	Operating temperature	-40 °C...85 °C
Installation temperature		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

System specifications

Number of poles	2	Mounting onto the PCB	SMD solder connection
Shielding	Yes	Side termination, characteristic	Clip-on flange
Transmission rate	10/100/1000 MBit/s	Type of connection	Solder connection
Category	T1-B	Product family	Industrial Ethernet
Protection degree	IP67 with housing	Plugging cycles	≥ 100
Outgoing elbow	180°	Performance-Category	T1-B 10/100/1000 MBit/s
Soldering process	Reflow soldering, Manual soldering	Solder pin dimensions	Octagonal

Electrical properties

Insulation resistance	≥ 500 MΩ	Nominal voltage	72 V
Rated current	4 A		

Standards

Connector standard	IEC 63171-5
--------------------	-------------

Material data

Insulating material	LCP	Colour	black
Colour chart (similar)	RAL 9011	Insulation resistance	≥ 500 MΩ
Moisture Level (MSL)	1	UL 94 flammability rating	V-0
Contact material	Copper alloy	Contact surface	Ni/Au
Operating temperature, min.	-40 °C	Operating temperature, max.	85 °C

Packing

Packaging	Tape	VPE length	327.00 mm
VPE width	327.00 mm	VPE height	52.00 mm

IE-PCB-SPM-P-180-SMD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Important note

Notes

Classifications

ETIM 8.0	EC002637	ETIM 9.0	EC002637
ETIM 10.0	EC002637	ECLASS 14.0	27-46-02-01
ECLASS 15.0	27-46-02-01		

