


**WIL-LWXXXX-2700D024-860SXX0.3BM12GXXXX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Product image**

The WIL-LED lights family: Only 8mm (9.4mm with magnet) high LED lamp for 24V DC with very high luminous efficacy and high lifespan (greater 60 000h). Very robust construction, by full potting and metal housing - waterproof (IP67). Due to its 2700K light color suitable for the various applications. Very easy to connect thanks to the M12 connection. Due to the low power consumption, a small enough power supply with 24V for operation.

**General ordering data**

Order No.	2796070000
Type	<a href="#">WIL-LWXXXX-2700D024-860SXX0.3BM12GXXXX</a>
GTIN (EAN)	4064675123200
Qty.	1 items

## Technical data

### Approvals

#### Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate no. (cULus)	E354496

### Dimensions and weights

Depth	40 mm	Depth (inches)	1.5748 inch
Height	8 mm	Height (inches)	0.315 inch
Width	860 mm	Width (inches)	33.8582 inch
Net weight	650 g		

### Temperatures

Operating temperature	-20 - 60°C
-----------------------	------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	bf1e8170-69bb-4440-b3e0-4da351a9a3b0
EPREL Registration number	1324793

### Cable technical specifications

Cable Material	PUR	Sheathing colour	black
Housing main material	hard anodised aluminium	Cable length	0.3 m
Core cross-section	0.34 mm <sup>2</sup>		

### Connection data

LED Modul is attachable	no	Version	pin, straight
Number of poles	2	Coding	A-coded
Connection thread	M12	Tightening torque	0.8 Nm
Wiring	Pin 4 (Strand: black) control white LED, Pin 3 (Strand: blue)		

### Electric data

Rated voltage	24 V DC	Rated current	1.21 A
Power	31.8 W	Dimmable	Yes

### General technical data

Type of connection	Pre-assembled cable	Electronic equipment on rolling stock	No
Recommended class according to UL for NEC Class 2 use of an power supply		Shape of the LED module	Rectangular
Number of LEDs	56	Light colour (CCT)	2700K, Warm white
Light current	3323 lm	Emitting angle	40 °

**Technical data**




Illumination level	1007 lux	Operating life	60.000 h
Type of mounting	Screw mounting	Drill hole spacing	845 mm
Impact resistance	IK05	Protection degree	IP67
Efficiency class (according to EU Directive No. 874/2012)	Not required		

**Material data**

Material of LED cover	ESG	Housing main material	hard anodised aluminium
Threaded ring material	PA	Material of end caps	PBT

**Classifications**

ETIM 8.0	EC000996	ETIM 9.0	EC000996
ETIM 10.0	EC000996	ECLASS 14.0	27-11-06-35
ECLASS 15.0	27-11-06-35		

**Drawings****Dimensioned drawing****Detailed drawing****Detailed drawing****Pole scheme**