


THM WO VIN 25.4/95.2 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

| | |
|------------|--|
| Version | THM, Conductor and cable markers, 14 - 7 mm, 25.4 x 38.1 mm, white |
| Order No. | 2799260000 |
| Type | THM WO VIN 25.4/95.2 WS |
| GTIN (EAN) | 4064675261025 |
| Qty. | 1000 items |

THM WO VIN 25.4/95.2 WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 0.07 mm | Depth (inches) | 0.0028 inch |
| Height | 25.4 mm | Height (inches) | 1 inch |
| Width | 38.1 mm | Width (inches) | 1.5 inch |
| Net weight | 0.54 g | | |

Temperatures

Operating temperature range -40...80 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

| | |
|---|--|
| Type of printing | neutral |
| Width | 38.1 mm |
| UL 94 flammability rating | V-0 |
| Operating temperature range, max. | 80 °C |
| Operating temperature range, min. | -40 °C |
| Colour | white |
| Halogen | Yes |
| Basic material | Vinyl film |
| Printed characters | without |
| Number of markers per packaging unit compatible printer | Form of supply Label reel |
| Number of markers per combination | 1 Label reel = Conductor and cable markers |
| Operating temperature range | -40...80 °C |
| Number per roll | 1000 |

Conductor and cable markers

| | | | |
|----------------------|-----------|----------------------------------|--------------------|
| Halogen | Yes | Conductor cross-section, max. | 38 mm ² |
| Conductor O.D., max. | 7 mm | Conductor O.D., min. | 14 mm |
| Conductor O.D. | 14 - 7 mm | Cross-section for connected wire | 38 mm ² |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |

