

## VG M20 - K 68

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Similar to illustration



In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

### General ordering data

Version	VG K (standard plastic cable gland), Cable glands, straight, M 20, 10 mm, OD min. 10 - OD max. 14 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), Polyamide 6
Order No.	<a href="#">2811470000</a>
Type	VG M20 - K 68
GTIN (EAN)	4064675292227
Qty.	50 items

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Height	31 mm	Height (inches)	1.2205 inch
Length	41 mm	Length (inches)	1.6142 inch
Net weight	12.69 g		

**Temperatures**

Operating temperature -40 °C...100 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
REACH SVHC No SVHC above 0.1 wt%

**Certificate numbers cable gland**

Certificate no. cable gland (UL)	E-199260 - BM 13	Certificate no. cable gland (cULus)	E-199260 - BM 13
Approval conditions	DNV, UL, cULus		

**General information**

Outer cable diameter, max.	14 mm	Outer cable diameter, min.	10 mm
Protection degree with GWDR	IP54, IP66, IP67, IP68 - 5 bar (30 min.)	Tightening torque	3.5 Nm
Silicone	No	UL 94 flammability rating	V-2
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Pitch of thread	1.5 mm	Halogen	Yes
Standards	EN/IEC 62444	AF size 1	27 mm
AF size	27 mm	Protection degree	IP54, IP66, IP67, IP68 - 5 bar (30 min.)
Cable gland	M 20	Basic material	Polyamide 6
Seal insert	CR	Sealing	CR
External thread	M 20	Internal thread	without
Length of thread	10 mm	Torque for cap nut, max.	4.50 Nm
Torque for lock nut, min.	3.00 Nm	Note: protection class	IP66 applications only possible with sealing ring for threaded connections. Without sealing ring for threaded connections, only IP54 is possible.
Torque for connecting adapter, max.	4.00 Nm	Torque for connecting adapter, min.	3.00 Nm
Torque for cap nut, min.	3.50 Nm	Torque for lock nut, max.	4.00 Nm

**Classifications**

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-01
ECLASS 15.0	27-14-08-01		