Data sheet

# SAIL-M12GM8W-3-2.5T0V

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Product image



## General ordering data

| | |
|---|---|
| Version | Sensor/actuator line, M12 / M8, Number of poles : 3, 2.5 m, Connecting line, Shielded: No, LED: No, Sheath material: PUR, Halogen: No |
| Order No. | 2812850250 |
| Type | SAIL-M12GM8W-3-2.5T0V |
| GTIN (EAN) | 4064675341833 |
| Qty. | 1 items |

# Data sheet

## SAIL-M12GM8W-3-2.5TOV

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

# Technical data

### Approvals

| | |
|---|---|
| Approvals | |
| ROHS | Conform |

### Dimensions and weights

| | |
|---|---|
| Net weight | 120 g |

### Environmental Product Compliance

| | |
|---|---|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | bd63baef-8092-4596-90c7-5b4daa22710b |

### Technical specifications for cable

| | | | |
|---|---|---|---|
| Cable length | 2.5 m | Sheathing colour | orange |
| Suitable for cable carriers | Yes | Core cross-section | 0.34 mm² |
| Shielded | No | Halogen | No |
| Bending radius, min., moving | 10 x cable diameter | Bending radius, min., stationary | 5 x cable diameter |
| Bending cycles | 12 Mio | Speed | 5 m/s |
| Sheath material | PUR | LABS-free | Yes |
| Outer cladding in accordance with UL AWM style | 20233 (80 °C / 300 V) | Core in accordance with UL AWM style | 10995 (80 °C / 300 V) |
| Irradiation crosslinked | No | Welding spark resistance | Yes |
| Colour coding | brown, blue, black | Torsion resistance | 360 °/m |
| Temperature range, stationary | -40...80 °C | Resistant to welding beads | Yes |
| Temperature range, moving | -25...80 °C | Number of poles | 3 |
| Outside diameter | 4.5 mm ± 0.2 mm | | |

### General technical data

| | | | |
|---|---|---|---|
| Coding | A-coded | Connection thread | M12 / M8 |
| Contact surface | Gold-plated | LED | No |
| Version | Connecting line | Housing main material | PUR |
| Nominal voltage | 24 V | Nominal current | 4 A |
| AF size | 12 mm | Protection degree | IP65, IP66, IP67, IP68, when screwed in |
| Pollution severity | 3 | Threaded ring material | Diecast zinc |
| Temperature range of housing | -25...+85 °C | | |

### Electrical properties

| | |
|---|---|
| Nominal voltage | 24 V |

### Plug, left

| | |
|---|---|
| Plug left | M12, A-coded, IP68, male contact, straight, Plastic |

# Data sheet

## SAIL-M12GM8W-3-2.5TOV

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

# Technical data

### Plug, right

| | |
|---|---|
| Plug right | M8, A-coded, IP68, female contact, angled 90°, Plastic |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 8.0 | EC001855 | ETIM 9.0 | EC001855 |
| ETIM 10.0 | EC001855 | ECLASS 14.0 | 27-06-03-11 |
| ECLASS 15.0 | 27-06-03-11 | | |

# SAIL-M12GM8W-3-2.5TOV

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

## Drawings


### Detailed drawing




### Dimensioned drawing





### Dimensioned drawing





### Pole scheme




### Pole scheme




### Wiring diagram



# SAIL-M12GM8W-3-2.5TOV

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Drawings

### The ideal tool: Screwty ® with torque function



Light, securely screwed-in round plug-in connectors. Screwty set DM / VPE: 1 / Order No.: 1920000000 Adapters: M12, M12 F, M8, M8 F