

**PAC-HE40-2HE20-V2-3M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

The pre-assembled PAC cables establish an electrical and logical connection between the PLC and the PLC interfaces. These cables consist of the following components:

- Manufacturer's PLC connector.
- Multi-pole LIYY or LY YCY cable (shielded) with a cross-section of 0.14 mm<sup>2</sup> or 0.25 mm<sup>2</sup>.
- Flat cable connector, SUB-D or RSV, for connection to the interface.

The cables are tested automatically for their continuity and insulation to guarantee the functionality for which they have been designed.

**General ordering data**

Version	Pre-assembled cable, PAC, Cable LiYY, 0.14 mm <sup>2</sup>
Order No.	<a href="#">2814160030</a>
Type	PAC-HE40-2HE20-V2-3M
GTIN (EAN)	409998660848 1
Qty.	1 items

**PAC-HE40-2HE20-V2-3M**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Net weight 425 g

**Temperatures**

Storage temperature -10...60 °C      Operating temperature -10...50 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant  
 REACH SVHC No SVHC above 0.1 wt%

**General Data**

Cable length	3 m	Suitable for	Digital signals
Basic material	PVC	Cable	Cable LiYY
Interface connector	2X FLAT CABLE CONNECTOR HE10 20P	Number of poles, min.	40-pole, 20-pole
Outer diameter	7,6 ± 1 mm	Connector PLC side	FLAT CABLE PLANO HE10 40P
Wire cross-section	0.14 mm <sup>2</sup>		

**Electrical Data**

Total current, max.	3 A	Permissible current strength per path, max.	1 A
Rated voltage	≤ 60 Vdc ≤ 25 Vac	Resistance	≤ 150 mΩ/m
Capacity wire / wires	300 pF/m		

**Classifications**

ETIM 8.0	EC000237	ETIM 9.0	EC000237
ETIM 10.0	EC000237	ECLASS 14.0	27-24-22-20
ECLASS 15.0	27-24-22-20		