

BIT E6,3 T20 X 150**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The Weidmüller bits are standard bits which are highly popular with users thanks to their good quality, large range and efficiency. The computer-controlled hardening method enables Weidmüller to guarantee a consistently high standard of quality.

The high-quality raw materials used make it possible to reach torques far higher than any of those specified in the relevant DIN standards:

- DIN 5261 for PH/PZ bits,
- DIN 5263 for slotted bits,
- Camcar standard for TORX bits

That means a long life at high torques and hence ideal conditions for standard situations.

The benefits:

- Suitable for all types of screws. Because of their excellent hardness values of 59-61 HRC, they are suitable for use with both manual and power tools.
- Good wearing resistance and thus a long life expectancy.
- Optimum fit in all DIN screws means low wear and optimum torque transmission.
- Manufactured to meet professional quality criteria according to relevant ISO standards with a consistently high standard of quality.

General ordering data

Version	Mounting tool
Order No.	2821510000
Type	BIT E6,3 T20 X 150
GTIN (EAN)	4064675359050
Qty.	5 items

BIT E6,3 T20 X 150

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data**Approvals**

ROHS	Conform
------	---------

Dimensions and weights

Width	150 mm	Width (inches)	5.9055 inch
Net weight	2 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Screwing tools

Form	Torx	Size	T20
------	------	------	-----

Classifications

ETIM 6.0	EC002117	ETIM 7.0	EC002117
ETIM 8.0	EC003864	ETIM 9.0	EC003864
ETIM 10.0	EC003864	ECLASS 9.0	21-04-42-02
ECLASS 9.1	21-01-90-90	ECLASS 10.0	21-04-42-02
ECLASS 11.0	21-04-42-02	ECLASS 12.0	21-04-42-02
ECLASS 13.0	21-04-42-02	ECLASS 14.0	21-04-42-02
ECLASS 15.0	21-04-42-02		