

**SAIL-M12GM8W-3L-0.6TOV**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Product image****General ordering data**

|            |  |
|------------|--|
| Version    | Sensor/actuator line, M12 / M8, Number of poles : 3, 0.6 m, Connecting line, Shielded: No, LED: Yes, Sheath material: PUR, Halogen: No |
| Order No.  | <a href="#">2812950060</a>   |
| Type       | SAIL-M12GM8W-3L-0.6TOV   |
| GTIN (EAN) | 4064675341635  |
| Qty.       | 1 items  |

**SAIL-M12GM8W-3L-0.6TOV**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergsstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Approvals**

Approvals



RoHS Conform

**Dimensions and weights**

Net weight 85 g

**Environmental Product Compliance**

RoHS Compliance Status Compliant with exemption

RoHS Exemption (if applicable/known) 6c, 7cl

REACH SVHC Lead 7439-92-1

SCIP bd63baef-8092-4596-90c7-5b4daa22710b

**Technical specifications for cable**

|  |                       |
|--|-----------------------|
| Cable length                                   | 0.6 m                 |
| Suitable for cable carriers                    | Yes                   |
| Shielded                                       | No                    |
| Bending radius, min., moving                   | 10 x cable diameter   |
| Bending cycles                                 | 12 Mio                |
| Sheath material                                | PUR                   |
| Outer cladding in accordance with UL AWM style | 20233 (80 °C / 300 V) |
| Irradiation crosslinked                        | No                    |
| Colour coding                                  | brown, blue, black    |
| Temperature range, stationary                  | -40..80 °C            |
| Temperature range, moving                      | -25..80 °C            |
| Outside diameter                               | 4.5 mm ± 0.2 mm       |

|                                      |                       |
|--------------------------------------|-----------------------|
| Sheathing colour                     | orange                |
| Core cross-section                   | 0.34 mm <sup>2</sup>  |
| Halogen                              | No                    |
| Bending radius, min., stationary     | 5 x cable diameter    |
| Speed                                | 5 m/s                 |
| LABS-free                            | Yes                   |
| Core in accordance with UL AWM style | 10995 (80 °C / 300 V) |
| Welding spark resistance             | Yes                   |
| Torsion resistance                   | 360 °/m               |
| Resistant to welding beads           | Yes                   |
| Number of poles                      | 3                     |

**General technical data**

|                              |                 |
|------------------------------|-----------------|
| Coding                       | A-coded         |
| Contact surface              | Gold-plated     |
| Version                      | Connecting line |
| Nominal voltage              | 24 V            |
| AF size                      | 12 mm           |
| Pollution severity           | 3               |
| Temperature range of housing | -25...+85 °C    |

|                        |   |
|------------------------|---|
| Connection thread      | M12 / M8                                |
| LED                    | Yes                                     |
| Housing main material  | PUR                                     |
| Nominal current        | 4 A                                     |
| Protection degree      | IP65, IP66, IP67, IP68, when screwed in |
| Threaded ring material | Diecast zinc                            |

**Electrical properties**

Nominal voltage 24 V

**Plug, left**

Plug left M12, A-coded, IP68, male contact, straight, Plastic

**SAIL-M12GM8W-3L-0.6TOV**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Plug, right**

|            |   |
|------------|---|
| Plug right | M8, A-coded, IP68, female<br>contact, angled 90°,<br>Plastic, LED |
|------------|---|






**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001855    | ETIM 9.0    | EC001855    |
| ETIM 10.0   | EC001855    | ECLASS 14.0 | 27-06-03-11 |
| ECLASS 15.0 | 27-06-03-11 |             |             |

**SAIL-M12GM8W-3L-0.6TOV**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings****Detailed drawing****Dimensioned drawing****Dimensioned drawing****Pole scheme****Pole scheme****Wiring diagram**

**SAIL-M12GM8W-3L-0.6TOV**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings****The ideal tool: Screwty® with torque function**

Light, securely screwed-in round plug-in  
connectors. Screwty set DM / VPE: 1 / Order No.:  
1920000000 Adapters: M12, M12 F, M8, M8 F

## SAIL-M12GM8W-3L-0.6TOV

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Cutting tools



Cutting tools for conductors up to 8 mm, 12 mm, 14 mm and 22 mm outside diameter. The special blade geometry allows pinch-free cutting of copper and aluminium conductors with minimum physical effort. The cutting tools (KT 8 to KT 22) also come with VDE and GS-tested protective insulation up to 1,000 V in accordance with EN/IEC 60900.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | KT 8                       | Version  |
| Order No.  | <a href="#">9002650000</a> | Cutting tools, Cutting tool for one-hand operation |
| GTIN (EAN) | 4008190020163              |  |
| Qty.       | 1 ST                       |  |

## Tools



Sheathing stripper for PVC cables

## General ordering data

|            |                            |                            |
|------------|----------------------------|----------------------------|
| Type       | AM 12                      | Version                    |
| Order No.  | <a href="#">9030060000</a> | Tools, Sheathing strippers |
| GTIN (EAN) | 4008190337827              |                            |
| Qty.       | 1 ST                       |                            |

## Screwty® cable gland tool with torque function



The ideal tool for any application  
Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

**SAIL-M12GM8W-3L-0.6TOV**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergsstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Accessories****General ordering data**

|            |                            |  |
|------------|----------------------------|--|
| Type       | SCREWTY-M12-DM             | Version                                |
| Order No.  | <a href="#">1900001000</a> | Cable gland tool for moulded M12 lines |
| GTIN (EAN) | 4032248436408              |  |
| Qty.       | 1 ST                       |  |
| Type       | SAI-SCREWTY BOX            | Version                                |
| Order No.  | <a href="#">1939180000</a> | Bolting tool                           |
| GTIN (EAN) | 4032248615506              |  |
| Qty.       | 1 ST                       |  |

**Tools**

- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

**General ordering data**

|            |                            |                            |
|------------|----------------------------|----------------------------|
| Type       | STRIPPER 6-16 RED-LINE     | Version                    |
| Order No.  | <a href="#">9203110000</a> | Stripping and cutting tool |
| GTIN (EAN) | 4032248541423              |                            |
| Qty.       | 1 ST                       |                            |


## SAIL-M12GM8W-3L-0.6TOV

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Blank



TM-I is an acknowledged and accredited marker type for traffic engineering applications. There are various different tag lengths available for individual labelling with long character strings. Easy handling of separation and installation thanks to the project marker field. Pre-attachment of sleeves and retrofitting of tags offer excellent versatility.

The special contour of TM-I allows easy assembly and secures firm positioning. They are compatible with a number of commercially available sleeves. Thanks to the MultiCard format, the tags can be printed quickly and conveniently with the PrintJet CONNECT, plotter or the STI pen.

- Easy handling of separation and installation thanks to the project marker field.
- Acknowledged and accredited marker for traffic engineering applications
- Pre-attachment of sleeves and retrofitting of tags offer excellent versatility
- Not suited for labelling with P-Ink or STI pen in connection with CLI T sleeves

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | TM-I 18 MC NE WS           | Version  |
| Order No.  | <a href="#">1718431044</a> | TM-I, Insert markers, 1.5 - 22 mm, 18 x 4 mm, white  |
| GTIN (EAN) | 4008190349011              |  |
| Qty.       | 320 ST                     |  |
| Type       | TM-I 18 MC NE GE           | Version  |
| Order No.  | <a href="#">1718431687</a> | TM-I, Insert markers, 1.5 - 22 mm, 18 x 4 mm, yellow |
| GTIN (EAN) | 4008190349028              |  |
| Qty.       | 320 ST                     |  |