

**SAIL-M8BG-4-2.0TOV**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**



**General ordering data**

|            |   |
|------------|---|
| Version    | Sensor/actuator line, M8, Number of poles : 4, 2 m, Female socket, straight, Shielded: No, LED: No, Sheath material: PUR, Halogen: No |
| Order No.  | <a href="#">2813030200</a>  |
| Type       | SAIL-M8BG-4-2.0TOV  |
| GTIN (EAN) | 4064675341321   |
| Qty.       | 1 items   |

## SAIL-M8BG-4-2.0TOV

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



|                         |                            |
|-------------------------|----------------------------|
| ROHS                    | Conform                    |
| UL File Number Search   | <a href="#">UL Website</a> |
| Certificate no. (cULus) | E307231                    |

## Dimensions and weights

|            |      |
|------------|------|
| Net weight | 75 g |
|------------|------|

## Environmental Product Compliance

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status               | Compliant with exemption             |
| RoHS Exemption (if applicable/known) | 6c                                   |
| REACH SVHC                           | Lead 7439-92-1                       |
| SCIP                                 | e8d8af70-4c85-4483-bc8c-9bc5b598e2a9 |

## Technical specifications for cable

|                                      |                       |  |                           |
|--------------------------------------|-----------------------|--|---------------------------|
| Cable length                         | 2 m                   | Sheathing colour                               | orange                    |
| Suitable for cable carriers          | Yes                   | Core cross-section                             | 0.34 mm <sup>2</sup>      |
| Shielded                             | No                    | Halogen  | No                        |
| Bending radius, min., moving         | 7.5 x cable diameter  | Bending radius, min., stationary               | 4 x cable diameter        |
| Bending cycles                       | 10 Mio                | Sheath material                                | PUR                       |
| LABS-free                            | Yes                   | Outer cladding in accordance with UL AWM style | 20233 (80 °C / 300 V)     |
| Core in accordance with UL AWM style | 10995 (80 °C / 300 V) | Irradiation crosslinked                        | No                        |
| Welding spark resistance             | Yes                   | Colour coding                                  | brown, blue, black, white |
| Torsion resistance                   | 360 °/m               | Temperature range, stationary                  | -40...80 °C               |
| Resistant to welding beads           | Yes                   | Temperature range, moving                      | -25...80 °C               |
| Number of poles                      | 4                     | Outside diameter                               | 4.9 mm ± 0.2 mm           |

## General technical data

|                    |                         |                              |  |
|--------------------|-------------------------|------------------------------|--|
| Coding             | A-coded                 | Connection thread            | M8   |
| Contact surface    | Gold-plated             | LED                          | No   |
| Version            | Female socket, straight | Housing main material        | PUR  |
| Nominal voltage    | 24 V                    | Nominal current              | 4 A  |
| AF size            | 12 mm                   | Protection degree            | IP65, IP66, IP67, IP68,<br>when screwed in |
| Pollution severity | 3                       | Temperature range of housing | -25...+85 °C                               |

## Electrical properties

|                 |      |
|-----------------|------|
| Nominal voltage | 24 V |
|-----------------|------|

## General standards

|                         |         |
|-------------------------|---------|
| Certificate no. (cULus) | E307231 |
|-------------------------|---------|

**SAIL-M8BG-4-2.0TOV**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Plug, left**

Plug left M8, A-coded, IP68, female contact, straight, Plastic

**Plug, right**

Plug right free conductor end

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001855    | ETIM 9.0    | EC001855    |
| ETIM 10.0   | EC001855    | ECLASS 14.0 | 27-06-03-11 |
| ECLASS 15.0 | 27-06-03-11 |             |             |

SAIL-M8BG-4-2.0TOV

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany


www.weidmueller.com

Drawings

Detailed drawing



Dimensioned drawing



Pole scheme



Wiring diagram



### The ideal tool: Screwty® with torque function

---



Light, securely screwed-in round plug-in connectors. Screwty set DM / VPE: 1 / Order No.: 1920000000 Adapters: M12, M12 F, M8, M8 F