

CRIMPFIX ECO



- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

General ordering data

Version	Automatic machines, Automatic stripper and crimper
Order No.	2833890000
Type	CRIMPFIX ECO
GTIN (EAN)	4064675422570
Qty.	1 items

CRIMPFIX ECO

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	323 mm	Depth (inches)	12.7165 inch
Height	188 mm	Height (inches)	7.4016 inch
Width	230 mm	Width (inches)	9.0551 inch
Net weight	12496 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cI
REACH SVHC	Lead 7439-92-1
SCIP	d2df479e-2b79-4e98-adc7-b03577df98ae

PW65 maintenance - automatic stripping/crimping

Stripping range	0.5 - 2.5 mm ² (~ AWG 20-14)	Drive	Electro-mechanical
Pulse time	approx. 1.5 s	Crimping	Trapezoidal
Wire end ferrules cross-section, max.	2.5 mm ²	Wire end ferrules cross-section, min.	0.5 mm ²
Crimping range, max.	2.5 mm ²	Crimping range, min.	0.5 mm ²
Crimping length	8 mm	Consumables	Linked wire-end ferrules
Length of wire-end ferrule	14 mm	Electrical connection	100-240 V / 50/60 Hz / 100 VA

Classifications

ETIM 8.0	EC002778	ETIM 9.0	EC002778
ETIM 10.0	EC002778	ECLASS 14.0	17-13-01-01
ECLASS 15.0	17-13-01-01		