

FUSE 10X38 16A 1000 VDC GPV S

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The gPV cylindrical fuse cartridges are designed to provide compact, safe and economical protection of photovoltaic modules (field protection) with voltages up to 1,500 DC. They provide protection against both overload and short circuit (gPV class according to the requirements of IEC60269-6 and UL248-19 standards). Made of a ceramic tube with high internal pressure and thermal shock resistance, allowing high switching capacity in a small space. The contacts are made of silver-plated copper and the fusible elements of pure silver to avoid ageing and thus keep the electrical characteristics invariable. They are available in the sizes 10x38 mm, 10x85 mm and 22x58 mm.

General ordering data

| | |
|------------|---|
| Version | Photovoltaics, Cartridge fuse, 1000 V, 10x38, gPV, 16 A |
| Order No. | 2837520000 |
| Type | FUSE 10X38 16A 1000 VDC GPV S |
| GTIN (EAN) | 4064675431039 |
| Qty. | 10 items |

FUSE 10X38 16A 1000 VDC GPV S

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

| | | | |
|----------|---------|-----------------|-------------|
| Height | 38 mm | Height (inches) | 1.4961 inch |
| Width | 10 mm | Width (inches) | 0.3937 inch |
| Diameter | 10.3 mm | Net weight | 9 g |

Temperatures

| | | | |
|---------------------|----------------|-----------------------------|-------------|
| Storage temperature | -40°C ... 90°C | Operating temperature range | -40...80 °C |
|---------------------|----------------|-----------------------------|-------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Fuse cartridge

| | | | |
|----------------------|--|-------------------------|-------|
| Fuse-link standard | IEC 60269-1, IEC 60269-6, gPV (EN 60269-6) | Current | 16 A |
| Rated DC voltage | 1000 V | Rated breaking capacity | 10 kA |
| Material of contacts | silver-plated | Power dissipation, max. | 3 W |

Classifications


| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002704 | ETIM 9.0 | EC002704 |
| ETIM 10.0 | EC002704 | ECLASS 14.0 | 27-14-20-02 |
| ECLASS 15.0 | 27-14-20-02 | | |

FUSE 10X38 16A 1000 VDC GPV S


Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Drawings




Derating curve




Ambient temperature derating factor curve

Graph



T-I characteristic curve

Graph



Power loss correction factor chart