

PVHXM-M-W+XX06M+11

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The Y cable is used for the parallel connection of several strings in a PV system, e.g. for splitting a line in front of an inverter.

The cables are available in different connection variants.

General ordering data

Version	Photovoltaics, X-Connector Cable, 2x MC4 Male, 1x WM4 C Female, 1x MC4 Female, 6mm ² , 1000 V
Order No.	2814260000
Type	PVHXM-M-W+XX06M+11
GTIN (EAN)	4064675298946
Qty.	1 items

PVHXM-M-W+XX06M+11

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Net weight 117.4 g

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

PV cable harnessing

PV cable version	Cable side	left
	Number	1
	Cable length	160 mm
	Cable colour	black
	Cable cross section	6 mm ²
	Rated current	39 A
	Inline fuse integrated	No
	Version of cable end [In-Block]	connector
	Connector version	MC 4
	Type of plug-in contact	male
	Cable side	right 1
	Number	1
	Cable length	200 mm
	Cable colour	black
	Cable cross section	6 mm ²
	Rated current	39 A
	Inline fuse integrated	No
	Version of cable end [In-Block]	connector
	Connector version	MC 4
	Type of plug-in contact	male
	Cable side	right 2
	Number	2
	Cable length	200 mm
	Cable colour	black
	Cable cross section	6 mm ²
	Rated current	35 A
	Inline fuse integrated	No
	Version of cable end [In-Block]	connector
	Connector version	WM4 C
	Type of plug-in contact	female
	Cable side	right
	Number	3
	Cable length	200 mm
	Cable colour	black
	Cable cross section	6 mm ²
	Rated current	39 A
Version of cable end [In-Block]	connector	
Connector version	MC 4	

PVHXM-M-W+XX06M+11

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

	Type of plug-in contact	female
Rated DC voltage	1100 V	
Wire cross-section	6.00 mm ²	

Electrical characteristics

Rated DC voltage	1100 V
------------------	--------

Classifications


ETIM 8.0	EC001576	ETIM 9.0	EC001576
ETIM 10.0	EC001576	ECLASS 14.0	27-06-04-02
ECLASS 15.0	27-06-04-02		

PVHXM-M-W+XX06M+11

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com



PVHXM-M-W+XX06M+11

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Drawings

www.weidmueller.com

