

## WPD 100 2X25/6X10 BK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



### Building installation wiring

For building installations, we offer a complete system that revolves around the 10×3 copper rail and comprises perfectly coordinated components: from installation terminal blocks, neutral conductor terminal blocks and distribution terminal blocks to comprehensive accessories such as busbars and busbar holders.

### General ordering data

Version	Potential distributor terminal, Screw connection, black, 25 mm <sup>2</sup> , 101 A, 1000 V, Number of connections: 8, Number of levels: 1
Order No.	<a href="#">2814490000</a>
Type	WPD 100 2X25/6X10 BK
GTIN (EAN)	4064675299721
Qty.	3 items

## WPD 100 2X25/6X10 BK

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

## Dimensions and weights

Depth	49 mm	Depth (inches)	1.9291 inch
Height	55.4 mm	Height (inches)	2.1811 inch
Width	30.2 mm	Width (inches)	1.189 inch
Net weight	102 g		

## Temperatures

Ambient temperature	-50 °C...85 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	130 °C		

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	9b5f0838-1f0b-4c14-9fc7-3f5e6ee75be2

## Material data

Basic material	Wemid	Colour	black
UL 94 flammability rating	V-0		

## System specifications

Version	Screw connection	End cover plate required	No
Number of potentials	1	Number of levels	1
Number of clamping points per level	2	Levels cross-connected internally	Yes
Mounting rail	TS 35	N-function	No
PE function	No	PEN function	No

## Additional technical data

Explosion-tested version	Yes	Type of mounting	Snap-on
--------------------------	-----	------------------	---------

## Conductors for clamping (additional connection)

Connection type, additional connection Screw connection

## Conductors for clamping (rated connection)

Wire connection cross section AWG, max.	AWG 4	Connection direction	on side
Type of connection 2	Screw connection	Type of connection	Screw connection
Number of connections	8	Clamping range, max.	25 mm <sup>2</sup>
Clamping range, min.	1.5 mm <sup>2</sup>	Wire connection cross section AWG, min.	AWG 16

## WPD 100 2X25/6X10 BK

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	1.5 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	16 mm <sup>2</sup>
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	1.5 mm <sup>2</sup>	Wire connection cross section, finely stranded, max.	0 mm <sup>2</sup>
Wire connection cross section, finely stranded, min.	1.5 mm <sup>2</sup>	Connection cross-section, stranded, max.	25 mm <sup>2</sup>
Connection cross-section, stranded, min.	1.5 mm <sup>2</sup>	Wire connection cross-section, solid core, max.	25 mm <sup>2</sup>
Wire connection cross-section, solid core, min.	1.5 mm <sup>2</sup>		

### General

Number of poles	1	Wire connection cross section AWG, max.	AWG 4
Wire connection cross section AWG, min.	AWG 16	Standards	UL 1059, IEC 60947-7-1
Mounting rail	TS 35		

### Rating data

Rated cross-section	25 mm <sup>2</sup>	Rated voltage	1000 V
Rated AC voltage	1000 V	Rated DC voltage	1000 V
Nominal current	101 A	Current at maximum wires	101 A
Standards	UL 1059, IEC 60947-7-1		

### Classifications


ETIM 8.0	EC000897	ETIM 9.0	EC000897
ETIM 10.0	EC000897	ECLASS 14.0	27-25-01-19
ECLASS 15.0	27-25-01-19		

WPD 100 2X25/6X10 BK

Weidmüller Interface GmbH & Co. KG  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

Drawings



Conductor connection data according to DIN EN 60998-1 (Cu), IEC 61238-1 class A (Cu+Al)

Output (x2)	Copper		Aluminum		Output (x6)	Copper		Aluminum	
	□-□	□-□	□-□	□-□		□-□	□-□	□-□	□-□
2x25 mm²	□-□	□-□	□-□	□-□	6x10 mm²	□-□	□-□	□-□	□-□
25 mm²				8 Nm	10 mm²				
18 mm²					8 mm²				
10 mm²			3 Nm		4 mm²				
6 mm²					2.5 mm²	2 Nm	2 Nm	3 Nm	
4 mm²					1.5 mm²				
2.5 mm²									
1.5 mm²									
Stripping lengths	17 mm				Stripping lengths	9 mm			
screw	M6 (+/- PZ2)				screw	M6 (+/- PZ2)			

□-□ Standed   
  □-□ Solid   
  □-□ Flexible with female

