

SFX-M 11/60 LRP AL SDR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

**General ordering data**

| | |
|------------|---|
| Version | MetalliCard, Conductor and cable markers, 7 - 40 mm, 60 x 11 mm, silver |
| Order No. | 2859530000 |
| Type | SFX-M 11/60 LRP AL SDR |
| GTIN (EAN) | 4064675572169 |
| Qty. | 1 items |

SFX-M 11/60 LRP AL SDR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 0.8 mm | Depth (inches) | 0.0315 inch |
| Height | 60 mm | Height (inches) | 2.3622 inch |
| Width | 11 mm | Width (inches) | 0.4331 inch |
| Net weight | 0.85 g | | |

Temperatures

Operating temperature range -55...130 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

| | | | |
|--------------------------------------|---|-------------|--|
| Number per sheet | 1 | | |
| Type of printing | To customer specification | | |
| Version | halogen-free | | |
| Width | 11 mm | | |
| Operating temperature range, max. | 130 °C | | |
| Operating temperature range, min. | -55 °C | | |
| Colour | silver | | |
| Basic material | Anodized aluminium | | |
| Printed characters | Requires M-Print PRO File | | |
| Number of markers per packaging unit | Form of supply | MetalliCard | |
| Size of labelling field | 11.2 x 45 mm | | |
| Recommended industries | Process, Energy | | |
| compatible printer | | | |
| Number of markers per combination | 1 MetalliCard = Conductor and cable markers | | |
| Operating temperature range | -55...130 °C | | |

Conductor and cable markers

| | | | |
|----------------------------------|--------------------------|-------------------------------|--------------------|
| Conductor cross-section, max. | 500 mm ² | Conductor cross-section, min. | 16 mm ² |
| Conductor O.D., max. | 40 mm | Conductor O.D., min. | 7 mm |
| Cable tie passage | Raised | Conductor O.D. | 7 - 40 mm |
| Cross-section for connected wire | 16 - 500 mm ² | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |

SFX-M 11/60 LRP AL SDR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

