

ZQV 2.5N/2 WT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

Version	Cross-connector (terminal), Plugged, white, 24 A, Number of poles: 2, Pitch in mm (P): 5.10, Insulated: Yes, Width: 7.9 mm
Order No.	2831560000
Type	ZQV 2.5N/2 WT
GTIN (EAN)	4064675416692
Qty.	60 items

ZQV 2.5N/2 WT

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	24.7 mm	Depth (inches)	0.9724 inch
Height	2.8 mm	Height (inches)	0.1102 inch
Width	7.9 mm	Width (inches)	0.311 inch
Net weight	1.12 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-60 °C...85 °C
Operating temperature	-60 °C...130 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	130 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	Wemid	Colour	white
UL 94 flammability rating	V-0		

Additional technical data

Type of fixing	Plugged	Explosion-tested version	Yes
Type of mounting	Direct mounting		

Dimensions

Pitch in mm (P)	5.10 mm
-----------------	---------

General

Number of poles	2
-----------------	---

Rating data

Rated voltage	400 V	Nominal current	24 A
---------------	-------	-----------------	------

Important note

Product information	Due to stability and temperature reasons It is only possible to break out 60% of contact elements. The usage of cross connectors reduces the rated voltage to 400 V. The voltage reduced to 25 V if cut cross connection with blank cut edges are used.
---------------------	---

Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		