
Data sheet

WAD 12N MC SDR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The WAD connector marker is suitable for W-series terminals and for the WEW 35/2 and ZEW 35/2 end brackets. The markers are available as blank markers, with custom printing or standard print with lightning symbol. The WAD MultiCard markers are suitable for labelling with PrintJet CONNECT printers.For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	Group markers, Cover, 33.3 x 12 mm, WDU 16N
Order No.	2866680000
Type	WAD 12N MC SDR
GTIN (EAN)	4064675604891
Qty.	8 items

WAD 12N MC SDR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Height	33.3 mm	Height (inches)	1.311 inch
Width	12 mm	Width (inches)	0.4724 inch
Net weight	1.86 g		

Temperatures

Operating temperature range	-40…100 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption	
REACH SVHC	No SVHC above 0.1 wt%	
Product Carbon Footprint	Cradle to gate	0.031 kg CO2 eq.

General data

Orientation of print	horizontal and vertical	
Width	12 mm	
UL 94 flammability rating	V-2	
Operating temperature range, max.	100 °C	
Operating temperature range, min.	-40 °C	
Halogen	No	
Basic material	Polyamide 66	
Printed characters	To customer specification	
Number of markers per packaging unit	Form of supply	MultiCard
Number of markers per combination	1 MultiCard = Cover	
Operating temperature range	-40…100 °C	
Application/manufacturer	WDU 16N	

Classifications

ETIM 8.0	EC000761	ETIM 9.0	EC000761
ETIM 10.0	EC000761	ECLASS 14.0	27-28-11-01
ECLASS 15.0	27-28-11-01		

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Drawing