



**CH-SMC-00.33-OVP180****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Base counter, gateway, control box and overvoltage protection device are connected with pre-assembled cable sets as point-to-point or Y-assembly. Weidmüller offers the right connection solutions for this, conforming to FNN and DIN-VDE 0603 standards. Pre-assembled power cables with 6kV overvoltage protection round up the portfolio.

**General ordering data**

Version	Smart Metering Cable Assemblies, 6 kV, Pin, Socket connector, IP20, 600 V, KB PUR US 2X1.5 GY XX 6KV, 0.33 m
Order No.	<a href="#">2853620033</a>
Type	CH-SMC-00.33-OVP180
GTIN (EAN)	4064675477518
Qty.	10 items

**CH-SMC-00.33-OVP180**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Diameter 6.4 mm Net weight 1 g

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General Technical Data**

Number of poles 2 Rated impulse withstand voltage 6 kV  
 Nominal voltage 600 V Nominal current 18.5 A  
 Protection degree IP20

**Technical Specifications Connector**

Connector	Connector description	Connector 1
	Cable entry	straight
	Housing main material	Plastic
	Number of poles	3
	Type	Male
	Individual components connector	<a href="#">SLF 5.08/03/180 SN OR BX SO</a>
	Connector description	Connector 2
	Cable entry	straight
	Housing main material	Plastic
	Number of poles	3
	Type	Female
	Individual components connector	<a href="#">BLF 5.08HC/03/180 SN OR BX SO</a>

**Technical specifications for cable**

Cable length	0.33 m	Line type	KB PUR US 2X1.5 GY XX 6KV
Sheathing colour	grey	Resistance to oils	Yes
Core cross-section	1.5 mm <sup>2</sup>	Number of wires	2
Shielded	No	Halogen	No
Insulation	PP	Temperature range, moving, max.	90 °C
Temperature range, moving, min.	-30 °C	Temperature range, stationary, max.	90 °C
Temperature range, stationary, min.	-40 °C	Cable Material	PUR/ TPE
Bending radius, min., moving	15 x cable diameter	Bending radius, min., stationary	10 x cable diameter
Outside diameter	6.4 mm ± 0.25 mm		

**Classifications**

ETIM 8.0	EC001576	ETIM 9.0	EC001576
ETIM 10.0	EC001576	ECLASS 14.0	27-06-04-02
ECLASS 15.0	27-06-04-02		

CH-SMC-00.33-OVP180

Weidmüller Interface GmbH & Co. KG  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

Drawings

www.weidmueller.com

