

KT MINI**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Cutting tools for conductors up to 8 mm, 12 mm, 14 mm and 22 mm outside diameter. The special blade geometry allows pinch-free cutting of copper and aluminium conductors with minimum physical effort. The cutting tools (KT 8 to KT 22) also come with VDE and GS-tested protective insulation up to 1,000 V in accordance with EN/IEC 60900.

General ordering data

Version	Cutting tools
Order No.	2876460000
Type	KT MINI
GTIN (EAN)	4064675664024
Qty.	1 items

KT MINI

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	9.5 mm	Depth (inches)	0.374 inch
Height	120 mm	Height (inches)	4.7244 inch
Width	42 mm	Width (inches)	1.6535 inch
Length	120 mm	Length (inches)	4.7244 inch
Net weight	91 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Technical data

Description of article	Cutting tool for up to 12 mm outer diameter	Version	One-hand mechanical
Operating voltage	0 V		

Cutting tools

Copper cable - solid, max. (AWG)	2 AWG	Copper cable - solid, max.	6 mm ²
Copper cable - flexible, max. (AWG)	6 AWG	Copper cable - flexible, max.	6 mm ²
Copper cable - stranded, max. (AWG)	4 AWG	Copper cable - stranded, max.	10 mm ²
Copper cable, max. diameter	7 mm	Operating voltage	0 V
Single-core aluminium cable, max.(mm ²)	6 mm ²	Stranded aluminium cable, max. (AWG)	4 AWG
Stranded aluminium cable, max (mm ²)	10 mm ²	Stranded aluminium cable, max. diameter	7 mm

Classifications

ETIM 8.0	EC000142	ETIM 9.0	EC000142
ETIM 10.0	EC000142	ECLASS 14.0	21-04-47-01
ECLASS 15.0	21-04-47-01		