


CC 74/101 MM GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Standard included: CC

Our systematically matching product range includes labels for identifying standardised components, as well as all-purpose and familiar formats such as the CC 85/54 marker for nameplates.

Your benefits with MultiMark

- “Different materials for various requirements”
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

General ordering data

| | |
|------------|---|
| Version | ClipCard, Device markers, 74 x 101 mm, yellow |
| Order No. | 2885770000 |
| Type | CC 74/101 MM GE |
| GTIN (EAN) | 4064675854371 |
| Qty. | 250 items |

CC 74/101 MM GE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 0.1 mm | Depth (inches) | 0.0039 inch |
| Height | 74 mm | Height (inches) | 2.9134 inch |
| Width | 101 mm | Width (inches) | 3.9764 inch |
| Net weight | 1.94 g | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General data

| | | | |
|-----------------------------------|-------------------|-----------------------------------|---------------|
| Adhesive | Acrylate adhesive | Version | Self-adhesive |
| Width | 101 mm | UL 94 flammability rating | V-0 |
| Operating temperature range, max. | 120 °C | Operating temperature range, min. | -40 °C |
| Colour | yellow | Halogen | No |
| Basic material | Polyester | Printed characters | neutral |

Device markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001288 | ETIM 9.0 | EC001288 |
| ETIM 10.0 | EC001288 | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 | | |