

## SFX-M 11/60 LRP ST SDR

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



### General ordering data

Version	MetalliCard, Conductor and cable markers, 7 - 40 mm, 60 x 11 mm, silver
Order No.	<a href="#">2859520000</a>
Type	SFX-M 11/60 LRP ST SDR
GTIN (EAN)	4064675572145
Qty.	1 items

## SFX-M 11/60 LRP ST SDR

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

## Technical data

www.weidmueller.com

## Dimensions and weights

Depth	0.8 mm	Depth (inches)	0.0315 inch
Height	60 mm	Height (inches)	2.3622 inch
Width	11 mm	Width (inches)	0.4331 inch
Net weight	0.85 g		

## Temperatures

Operating temperature range	-55...130 °C
-----------------------------	--------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## General data

Type of printing	To customer specification	
Width	11 mm	
Operating temperature range, max.	130 °C	
Operating temperature range, min.	-55 °C	
Colour	silver	
Basic material	Stainless steel 1.4301	
Number of markers per packaging unit	Form of supply	MetalliCard
Size of labelling field	11.2 x 45 mm	
Recommended industries	Process, Energy	
compatible printer		
Number of markers per combination	1 MetalliCard = Conductor and cable markers	
Operating temperature range	-55...130 °C	

## Conductor and cable markers

Conductor cross-section, max.	500 mm <sup>2</sup>	Conductor cross-section, min.	16 mm <sup>2</sup>
Conductor O.D., max.	40 mm	Conductor O.D., min.	7 mm
Cable tie passage	Raised	Conductor O.D.	7 - 40 mm
Cross-section for connected wire	16 - 500 mm <sup>2</sup>		

## Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

**SFX-M 11/60 LRP ST SDR**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

