Data sheet

# WAD 12N MC NE WS

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The WAD connector marker is suitable for W-series terminals and for the WEW 35/2 and ZEW 35/2 end brackets. The markers are available as blank markers, with custom printing or standard print with lightning symbol. The WAD MultiCard markers are suitable for labelling with PrintJet CONNECT printers.For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

| | |
|---|---|
| Version | Group markers, Cover, 33.3 x 12 mm, WDU 16N, white |
| Order No. | 2866660000 |
| Type | WAD 12N MC NE WS |
| GTIN (EAN) | 4064675604877 |
| Qty. | 32 items |

# Data sheet

## WAD 12N MC NE WS

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

# Technical data

### Approvals

| | |
|---|---|
| ROHS | Conform |

### Dimensions and weights

| | | | |
|---|---|---|---|
| Height | 33.3 mm | Height (inches) | 1.311 inch |
| Width | 12 mm | Width (inches) | 0.4724 inch |
| Net weight | 1.24 g | | |

### Temperatures

| | |
|---|---|
| Operating temperature range | -40…100 °C |

### Environmental Product Compliance

| | | |
|---|---|---|
| RoHS Compliance Status | Compliant without exemption | |
| REACH SVHC | No SVHC above 0.1 wt% | |
| Product Carbon Footprint | Cradle to gate | 0.026 kg CO2 eq. |

### General data

| | | |
|---|---|---|
| Orientation of print | horizontal and vertical | |
| Width | 12 mm | |
| UL 94 flammability rating | V-2 | |
| Operating temperature range, max. | 100 °C | |
| Operating temperature range, min. | -40 °C | |
| Colour | white | |
| Halogen | No | |
| Basic material | Polyamide 66 | |
| Printed characters | neutral | |
| Number of markers per packaging unit | Form of supply | MultiCard |
| Number of markers per combination | 1 MultiCard = Cover | |
| Operating temperature range | -40…100 °C | |
| Application/manufacturer | WDU 16N | |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 8.0 | EC000761 | ETIM 9.0 | EC000761 |
| ETIM 10.0 | EC000761 | ECLASS 14.0 | 27-28-11-01 |
| ECLASS 15.0 | 27-28-11-01 | | |

# WAD 12N MC NE WS

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Drawings



### Drawing