


**WIL-LRGBW-RXSS-XXXX-X610SX-M12X-X0**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Our L-series, as standard and premium variants, is the ideal surface mounted light for the industrial field. The swiveling mounting brackets allow for easy and direct mounting and positioning of the illumination field. With only one power supply, it is possible to connect several lights in series. Simple connection technology with circular connectors enables plug-and-play. A special safety glass protects against industrial influences and at the same time provides homogeneous illumination in the light color 5.700K.

**General ordering data**

Order No.	2899540000
Type	<a href="#">WIL-LRGBW-RXSS-XXXX-X610SX-M12X-X0</a>
GTIN (EAN)	4064675906599
Qty.	1 items

**WIL-LRGBW-RXSS-XXXX-X610SX-M12X-X0**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**
**Approvals**

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E354496

**Dimensions and weights**

Depth	40 mm	Depth (inches)	1.5748 inch
Height	42 mm	Height (inches)	1.6535 inch
Width	610 mm	Width (inches)	24.0157 inch
Net weight	770 g		

**Temperatures**

Operating temperature -20 - 45°C

**Environmental Product Compliance**

RoHS Compliance Status Compliant with exemption

RoHS Exemption (if applicable/known) 6c

REACH SVHC Lead 7439-92-1

SCIP b1b97d04-507a-4265-bbfb-4e884ff5d5a9

**Cable technical specifications**

Housing main material hard anodised aluminium

**Connection data**

LED Modul is attachable	no	Version	pin, straight
Number of poles	5	Coding	A-coded
Connection thread	M12	Wiring	Pin 1 - 4: control multicolor LED, Pin 5: GND(-)

**Electric data**

Rated voltage 24 V DC Power 38.7 W

**General technical data**

Type of connection	Pin connector	Electronic equipment on rolling stock	No
Light colour (CCT)	Red, Green, Blue, White	Emitting angle	100 °
Illumination level	372 lux	Operating life	60.000 h
Type of mounting	Screw mounting	Drill hole spacing	640 mm
Protection degree	IP67	Efficiency class (according to EU Directive No. 874/2012)	Not required

**Material data**

Material of LED cover PMMA Housing main material hard anodised aluminium

**WIL-LRGBW-RXSS-XXXX-X610SX-M12X-X0**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

**Classifications**

ETIM 8.0	EC000996	ETIM 9.0	EC000996
ETIM 10.0	EC000996	ECLASS 14.0	27-11-06-35
ECLASS 15.0	27-11-06-35		



## WIL-LRGBW-RXSS-XXXX-X610SX-M12X-X0

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Accessories

### Screw terminal connector



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.

The screw connection can be used in a wide range of applications. With this technology the conductor, optionally with wire-end ferrules, can be plugged into connection elements and secured with a screw. It is the classic, cheapest form of connection technology that also supports multi-conductor connections.

### General ordering data

Type	SAIBGS-P-5A-4/6-M12	Version
Order No.	<a href="#">9457250000</a>	Field attachable connector, M12
GTIN (EAN)	4032248155774	
Qty.	1 ST	

### PUR halogen-free black (U)



Sensor/actuator cables are used for wiring sensors and actuators and for transmitting data or power in various applications. The moulded cable offers connected and tested connection of the plug-in connector to the cable ex-works. The cables may be exposed to a wide range of conditions, such as humidity, dust, heat, cold, shock or vibration.

Our developers have focused specifically on this issue and designed a host of different M8 and M12 sensor-actuator cables so you are bound to find the solution you need for your application.

Is there something you have not managed to find or you feel needs explanation? Talk to us!

### General ordering data

Type	SAIL-M12BG-5-1.5U	Version
Order No.	<a href="#">9457910150</a>	Sensor/actuator line, One end without connector, M12, Number of poles : 5, 1.5 m, Female socket, straight, Shielded: No, LED: No,
GTIN (EAN)	4032248528875	Sheath material: PUR, Halogen: No
Qty.	1 ST	
Type	SAIL-M12BG-5-3.0U	Version
Order No.	<a href="#">9457910300</a>	Sensor/actuator line, One end without connector, M12, Number of poles : 5, 3 m, Female socket, straight, Shielded: No, LED: No, Sheath material: PUR, Halogen: No
GTIN (EAN)	4032248228843	
Qty.	1 ST	
Type	SAIL-M12BG-5-5.0U	Version
Order No.	<a href="#">9457910500</a>	Sensor/actuator line, One end without connector, M12, Number of poles : 5, 5 m, Female socket, straight, Shielded: No, LED: No, Sheath material: PUR, Halogen: No
GTIN (EAN)	4032248228850	
Qty.	1 ST	
Type	SAIL-M12BG-5-10U	Version
Order No.	<a href="#">9457911000</a>	Sensor/actuator line, One end without connector, M12, Number of poles : 5, 10 m, Female socket, straight, Shielded: No, LED: No,
GTIN (EAN)	4032248228867	Sheath material: PUR, Halogen: No
Qty.	1 ST	

## WIL-LRGBW-RXSS-XXXX-X610SX-M12X-X0

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

Type	SAIL-M12GM12G-5-1.0U	Version
Order No.	<a href="#">9457340100</a>	Sensor/actuator line, Connecting line, M12 / M12, Number of poles :
GTIN (EAN)	4032248832583	5, 1 m, pin, straight - socket, straight, Shielded: No, LED: No, Sheath
Qty.	1 ST	material: PUR, Halogen: No
Type	SAIL-M12GM12G-5-2.0U	Version
Order No.	<a href="#">9457340200</a>	Sensor/actuator line, Connecting line, M12 / M12, Number of poles :
GTIN (EAN)	4008190311285	5, 2 m, pin, straight - socket, straight, Shielded: No, LED: No, Sheath
Qty.	1 ST	material: PUR, Halogen: No
Type	SAIL-M12GM12G-5-3.0U	Version
Order No.	<a href="#">9457340300</a>	Sensor/actuator line, Connecting line, M12 / M12, Number of poles :
GTIN (EAN)	4008190311896	5, 3 m, pin, straight - socket, straight, Shielded: No, LED: No, Sheath
Qty.	1 ST	material: PUR, Halogen: No