

SAI-04D-VPPP-5A-M12O-1:1-EX**Weidmüller Interface GmbH & Co. KG**Klingenbergsstraße 26
D-32758 Detmold
Germanywww.weidmueller.com

Passive M12 distributors are available in all conceivable forms and configurations. Furthermore, a number of special versions, e.g. SAI distributors for EX zones or the ergonomic M8, are available only from Weidmüller. These innovative products are backed up by numerous proprietary rights.

General ordering data

Version	Hood version Ex, M12, 30 V, A-coded, LED: No, LED initiator: No, Wiring type: 1:1
Order No.	2902950000
Type	SAI-04D-VPPP-5A-M12O-1:1-EX
GTIN (EAN)	4099986005556
Qty.	1 items

SAI-04D-VPPP-5A-M120-1:1-EX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



Dimensions and weights

Depth	60 mm	Depth (inches)	2.3622 inch
Height	41.5 mm	Height (inches)	1.6339 inch
Length	102 mm	Length (inches)	4.0157 inch
Net weight	194.48 g		

Temperatures

Operating temperature -40 - 60°C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Connection data

Wire connection method	PUSH IN	Cable gland	M 20
Clamping range, min.	0.14 mm ²	Clamping range, max.	1.5 mm ²
Wire connection cross section AWG, min.	AWG 26	Wire connection cross section AWG, max.	AWG 16
Solid, min. H05(07) V-U	0.14 mm ²	Solid, max. H05(07) V-U	1.5 mm ²
Flexible, min. H05(07) V-K	0.14 mm ²	Flexible, max. H05(07) V-K	1.5 mm ²
w. plastic collar ferrule, DIN 46228 pt 4, min.	0.28 mm ²	w. plastic collar ferrule, DIN 46228 pt 4, max.	1 mm ²
w. wire end ferrule, DIN 46228 pt 1, min.	0.25 mm ²	w. wire end ferrule, DIN 46228 pt 1, max.	1 mm ²
Distributor outlet	Hood version Ex		

Electrical data

Rated voltage, min.	0 V	Rated voltage, max.	30 V
Max. current-carrying capacity per slot	0.8 A	Total current	0.8 A
Current per signal	0.8 A		

General technical data

Protection degree	IP66, IP67	Surge voltage category	III
Plug-in station coding	A-coded	Number of poles	5
Number of contact sockets	4	Connection thread	M12
Pollution severity	3	Fire behaviour	V-0
Plugging cycles	≤ 50	LED	No
LED initiator	No		

Material data

Material O-Ring	FKM	Housing main material	Pocan
Housing colour	black (similar to RAL 9005)	Hood sealing material	Polyurethane foamed

SAI-04D-VPPP-5A-M120-1:1-EX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Screw socket	Nickel-plated CuZn	Contact material	CuZn
Contact surface	Gold-plated	Contact carrier material	PBT (UL 94 VO)
Cable gland material	Plastic		

Important note

Product information	Included in delivery: • 2 x Protection cap M12 • 1 x Cable gland M20x1.5 • 1 x MultiCard ESG 9/20 Device marker
---------------------	--

Classifications

ETIM 8.0	EC003558	ETIM 9.0	EC003558
ETIM 10.0	EC003558	ECLASS 14.0	27-44-01-11
ECLASS 15.0	27-44-01-11		

SAI-04D-VPPP-5A-M12O-1:1-EX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings


Similar to illustration




Similar to illustration




Miscellaneous



Dimensioned drawing



Wiring diagram



SAI-04D-VPPP-5A-M120-1:1-EX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Passive M12 distributors are available in all conceivable forms and configurations. Furthermore, a number of special versions, e.g. SAI distributors for EX zones or the ergonomic M8, are available only from Weidmüller. These innovative products are backed up by numerous proprietary rights.

General ordering data

Type	SAI-TS35 MF	Version
Order No.	1917400000	
GTIN (EAN)	4032248551330	
Qty.	1 ST	

M12

Protective caps protect unassigned plug-in stations against external influences.

General ordering data

Type	SAI-SK-M12-UNI 2029	Version
Order No.	2330260000	
GTIN (EAN)	4032248592067	Protected component assemblies, Protective cap
Qty.	20 ST	

Blank

ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

SAI-04D-VPPP-5A-M120-1:1-EX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

General ordering data

Type	ESG 9/20 MC NE WS	Version
Order No.	1609940000	ESG, Device markers x 20 mm, PA 66, Colour: white, pluggable
GTIN (EAN)	4008190203528	
Qty.	200 ST	

Screwty® cable gland tool with torque function




The ideal tool for any application

Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

General ordering data

Type	SCREWTY SET -DM	Version
Order No.	1920000000	Cable gland tool for M8, M12 lines and connectors
GTIN (EAN)	4032248436859	
Qty.	1 ST	

2-pole, A-coded



Sensor cables for use in Ex applications with intrinsically safe circuits. Please refer to the manufacturer's declaration in the product downloads for further Information

General ordering data

Type	SAIL-M12G-2-5.0UBL	Version
Order No.	3107950500	Sensor/actuator line, One end without connector, M12, Number of
GTIN (EAN)	4099987797801	poles : 2, 5 m, pin, straight, Shielded: No, LED: No, Sheath material:
Qty.	1 ST	PUR, Halogen: No


SAI-04D-VPPP-5A-M12O-1:1-EX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

5-pole, A-coded




Sensor cables for use in Ex applications with intrinsically safe circuits. Please refer to the manufacturer's declaration in the product downloads for further Information

General ordering data

Type	SAIL-M12G-5-5.0UBL	Version
Order No.	3107980500	Sensor/actuator line, One end without connector, M12, Number of
GTIN (EAN)	4099987808064	poles : 5, 5 m, pin, straight, Shielded: No, LED: No, Sheath material:
Qty.	1 ST	PUR, Halogen: No

2-pole, A-coded




Sensor cables for use in Ex applications with intrinsically safe circuits. Please refer to the manufacturer's declaration in the product downloads for further Information

General ordering data

Type	SAIL-M12BG-2-5.0UBL	Version
Order No.	3107940500	Sensor/actuator line, One end without connector, M12, Number of
GTIN (EAN)	4099987795746	poles : 2, 5 m, Female socket, straight, Shielded: No, LED: No, Sheath
Qty.	1 ST	material: PUR, Halogen: No

5-pole, A-coded



Sensor cables for use in Ex applications with intrinsically safe circuits. Please refer to the manufacturer's declaration in the product downloads for further Information

General ordering data

Type	SAIL-M12BG-5-5.0UBL	Version
Order No.	3107970500	Sensor/actuator line, One end without connector, M12, Number of
GTIN (EAN)	4099987803854	poles : 5, 5 m, Female socket, straight, Shielded: No, LED: No, Sheath
Qty.	1 ST	material: PUR, Halogen: No


SAI-04D-VPPP-5A-M12O-1:1-EX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

2-pole, A-coded




Sensor cables for use in Ex applications with intrinsically safe circuits. Please refer to the manufacturer's declaration in the product downloads for further Information

General ordering data

Type	SAIL-M12W-2-5.0UBL	Version
Order No.	3107960500	Sensor/actuator line, One end without connector, M12, Number of
GTIN (EAN)	4099987802215	poles : 2, 5 m, pin, 90°, Shielded: No, LED: No, Sheath material: PUR,
Qty.	1 ST	Halogen: No

5-pole, A-coded




Sensor cables for use in Ex applications with intrinsically safe circuits. Please refer to the manufacturer's declaration in the product downloads for further Information

General ordering data

Type	SAIL-M12W-5-5.0UBL	Version
Order No.	3107990500	Sensor/actuator line, One end without connector, M12, Number of
GTIN (EAN)	4099987808101	poles : 5, 5 m, pin, 90°, Shielded: No, LED: No, Sheath material: PUR,
Qty.	1 ST	Halogen: No

2-pole, A-coded



Sensor cables for use in Ex applications with intrinsically safe circuits. Please refer to the manufacturer's declaration in the product downloads for further Information

General ordering data

Type	SAIL-M12GM12G-2-5.0UBL	Version
Order No.	2955200500	Sensor/actuator line, Connecting line, M12, Number of poles : 2, 5 m,
GTIN (EAN)	4099987802819	pin, straight - socket, straight, Shielded: No, LED: No, Sheath material:
Qty.	1 ST	PUR, Halogen: No


SAI-04D-VPPP-5A-M12O-1:1-EX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

5-pole, A-coded




Sensor cables for use in Ex applications with intrinsically safe circuits. Please refer to the manufacturer's declaration in the product downloads for further Information

General ordering data

Type	SAIL-M12GM12G-5-5.0UBL	Version
Order No.	2955210500	Sensor/actuator line, Connecting line, M12, Number of poles : 5, 5 m,
GTIN (EAN)	4099987808293	pin, straight - socket, straight, Shielded: No, LED: No, Sheath material:
Qty.	1 ST	PUR, Halogen: No

2-pole, A-coded



Sensor cables for use in Ex applications with intrinsically safe circuits. Please refer to the manufacturer's declaration in the product downloads for further Information

General ordering data

Type	SAIL-M12G-2SD5.0UBL	Version
Order No.	3108010500	Sensor/actuator line, One end without connector, M12, Number of
GTIN (EAN)	4099987813273	poles : 2, 5 m, pin, straight, Shielded: Yes, LED: No, Sheath material:
Qty.	1 ST	PUR, Halogen: No

4-pole, A-coded



Sensor cables for use in Ex applications with intrinsically safe circuits. Please refer to the manufacturer's declaration in the product downloads for further Information

General ordering data

Type	SAIL-M12G-4SD5.0UBL	Version
Order No.	3108030500	Sensor/actuator line, One end without connector, M12, Number of
GTIN (EAN)	4099987834346	poles : 4, 5 m, pin, straight, Shielded: Yes, LED: No, Sheath material:
Qty.	1 ST	PUR, Halogen: No


SAI-04D-VPPP-5A-M12O-1:1-EX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

2-pole, A-coded




Sensor cables for use in Ex applications with intrinsically safe circuits. Please refer to the manufacturer's declaration in the product downloads for further Information

General ordering data

Type	SAIL-M12BG-2SD5.0UBL	Version
Order No.	3108000500	Sensor/actuator line, One end without connector, M12, Number of
GTIN (EAN)	4099987808507	poles : 2, 5 m, Female socket, straight, Shielded: Yes, LED: No, Sheath
Qty.	1 ST	material: PUR, Halogen: No

4-pole, A-coded




Sensor cables for use in Ex applications with intrinsically safe circuits. Please refer to the manufacturer's declaration in the product downloads for further Information

General ordering data

Type	SAIL-M12BG-4SD5.0UBL	Version
Order No.	3106100500	Sensor/actuator line, One end without connector, M12, Number of
GTIN (EAN)	4099987175678	poles : 4, 5 m, Female socket, straight, Shielded: Yes, LED: No, Sheath
Qty.	1 ST	material: PUR, Halogen: No

2-pole, A-coded



Sensor cables for use in Ex applications with intrinsically safe circuits. Please refer to the manufacturer's declaration in the product downloads for further Information

General ordering data

Type	SAIL-M12W-2SD5.0UBL	Version
Order No.	3108020500	Sensor/actuator line, One end without connector, M12, Number of
GTIN (EAN)	4099987814584	poles : 2, 5 m, pin, 90°, Shielded: Yes, LED: No, Sheath material: PUR,
Qty.	1 ST	Halogen: No


SAI-04D-VPPP-5A-M120-1:1-EX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

4-pole, A-coded




Sensor cables for use in Ex applications with intrinsically safe circuits. Please refer to the manufacturer's declaration in the product downloads for further Information

General ordering data

Type	SAIL-M12W-4SD5.0UBL	Version
Order No.	3108040500	Sensor/actuator line, One end without connector, M12, Number of
GTIN (EAN)	4099987835138	poles : 4, 5 m, pin, 90°, Shielded: Yes, LED: No, Sheath material: PUR,
Qty.	1 ST	Halogen: No

2-pole, A-coded




Sensor cables for use in Ex applications with intrinsically safe circuits. Please refer to the manufacturer's declaration in the product downloads for further Information

General ordering data

Type	SAIL-M12GM12G-2SD5.0UBL	Version
Order No.	2993610500	Sensor/actuator line, Connecting line, M12, Number of poles : 2, 5 m,
GTIN (EAN)	4099987814881	pin, straight - socket, straight, Shielded: Yes, LED: No, Sheath material:
Qty.	1 ST	PUR, Halogen: No

4-pole, A-coded



Sensor cables for use in Ex applications with intrinsically safe circuits. Please refer to the manufacturer's declaration in the product downloads for further Information

General ordering data

Type	SAIL-M12GM12G-4SD5.0UBL	Version
Order No.	2955220500	Sensor/actuator line, Connecting line, M12, Number of poles : 4, 5 m,
GTIN (EAN)	4099987836265	pin, straight - socket, straight, Shielded: Yes, LED: No, Sheath material:
Qty.	1 ST	PUR, Halogen: No