

PZ 2.5 S

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Crimping tools for wire end ferrules, with and without plastic collars

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

| | |
|------------|--|
| Version | 0.14mm ² , 2.5mm ² , Trapezoidal crimp |
| Order No. | 2903690000 |
| Type | PZ 2.5 S |
| GTIN (EAN) | 4099986027008 |
| Qty. | 1 items |

PZ 2.5 S

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 31 mm | Depth (inches) | 1.2205 inch |
| Height | 70 mm | Height (inches) | 2.7559 inch |
| Width | 160 mm | Width (inches) | 6.2992 inch |
| Length | 160 mm | Length (inches) | 6.2992 inch |
| Net weight | 290.6 g | | |

Environmental Product Compliance

| | |
|------------------------|--------------------------------------|
| RoHS Compliance Status | Not affected |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 2159813b-98fd-4068-b62a-bc89a046c012 |

Technical data

| | |
|---------|---|
| Version | Mechanical, without interchangeable inserts |
|---------|---|

Description of contact

| | | | |
|-----------------------------------|--|-----------------------------------|---------------------|
| Type of contact | Wire-end ferrules with/without plastic collars | Conductor cross-section, max. AWG | AWG 14 |
| Conductor cross-section, min. AWG | AWG 26 | Crimping range, max. | 2.5 mm ² |
| Crimping range, min. | 0.14 mm ² | | |

tool data crimping

| | | | |
|---------------------------------------|---------------------|---------------------------------------|----------------------|
| Wire end ferrules cross-section, max. | 2.5 mm ² | Wire end ferrules cross-section, min. | 0.14 mm ² |
| Crimping type/profile | Trapezoidal crimp | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000168 | ETIM 9.0 | EC000168 |
| ETIM 10.0 | EC000168 | ECLASS 14.0 | 21-04-38-11 |
| ECLASS 15.0 | 21-04-38-11 | | |