


**SFC-DS 0/12 MC NE WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**SFC – SlimFix Clip MultiCard with two labelling fields**

For conductor markers, it is often required to quickly read the start and destination designation of the respective conductor. Here it makes sense to print both data directly on a marker.

The new SFC-DS markers are designed as MultiCards and are suitable for direct printing with our PrintJet printing system. Their two labelling areas allow multiple data to be printed on a single marker. The print data can be imported directly from CAE projects into the M-Print® PRO marking software. After printing, the markers are placed around the conductor and securely fixed with a special locking mechanism.

**General ordering data**

Version	Conductor and cable markers, 12 x 4.2 mm, white
Order No.	<a href="#">2904970000</a>
Type	SFC-DS 0/12 MC NE WS
GTIN (EAN)	4099986918481
Qty.	200 items

## SFC-DS 0/12 MC NE WS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	3.2 mm	Depth (inches)	0.126 inch
Height	12 mm	Height (inches)	0.4724 inch
Width	4.2 mm	Width (inches)	0.1654 inch
Net weight	0.31 g		

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.003 kg CO2 eq.	

## General data

Type of printing	neutral	Version	with snap-in foot
Width	4.2 mm	UL 94 flammability rating	UL 94, V-2
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Colour	white	Halogen	No
Basic material	Polyamide 66	Printed characters	without
Size of labelling field	11 x 2.2 mm	Number per roll	40

## Conductor and cable markers

Halogen	No	Conductor cross-section, max.	1 mm <sup>2</sup>
Conductor O.D., max.	2.5 mm	Conductor O.D., min.	1.5 mm
Cross-section for connected wire	1 mm <sup>2</sup>		

## Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

