


SFC-DS 3/21 MC NE GE**Weidmüller Interface GmbH & Co. KG**Klingenbergsstraße 26
D-32758 Detmold
Germanywww.weidmueller.com**SFC – SlimFix Clip MultiCard with two labelling fields**

For conductor markers, it is often required to quickly read the start and destination designation of the respective conductor. Here it makes sense to print both data directly on a marker.

The new SFC-DS markers are designed as MultiCards and are suitable for direct printing with our PrintJet printing system. Their two labelling areas allow multiple data to be printed on a single marker. The print data can be imported directly from CAE projects into the M-Print® PRO marking software. After printing, the markers are placed around the conductor and securely fixed with a special locking mechanism.

General ordering data

| | |
|------------|--|
| Version | Conductor and cable markers, 21 x 7 mm, yellow |
| Order No. | 2905190000 |
| Type | SFC-DS 3/21 MC NE GE |
| GTIN (EAN) | 4099986918887 |
| Qty. | 120 items |

SFC-DS 3/21 MC NE GE

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 6 mm | Depth (inches) | 0.2362 inch |
| Height | 21 mm | Height (inches) | 0.8268 inch |
| Width | 7 mm | Width (inches) | 0.2756 inch |
| Net weight | 0.68 g | | |

Environmental Product Compliance

| | |
|--------------------------|---|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |
| Product Carbon Footprint | Cradle to gate 0.004 kg CO ₂ eq. |

General data

| | | | |
|-----------------------------------|--------------|-----------------------------------|-------------------|
| Type of printing | neutral | Version | with snap-in foot |
| Width | 7 mm | UL 94 flammability rating | V-2, UL 94 |
| Operating temperature range, max. | 100 °C | Operating temperature range, min. | -40 °C |
| Colour | yellow | Halogen | No |
| Basic material | Polyamide 66 | Printed characters | without |
| Size of labelling field | 20 x 5 mm | Number per roll | 24 |

Conductor and cable markers

| | | | |
|----------------------------------|--------------------|-------------------------------|--------------------|
| Halogen | No | Conductor cross-section, max. | 10 mm ² |
| Conductor O.D., max. | 7 mm | Conductor O.D., min. | 4.5 mm |
| Cross-section for connected wire | 10 mm ² | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |

SFC-DS 3/21 MC NE GE

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

