

## VPU AC II+III 3+1 275/40 S

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



### General ordering data

Version	Surge voltage arrester, Low voltage, TN-S, TT
Order No.	<a href="#">2907770000</a>
Type	VPU AC II+III 3+1 275/40 S
GTIN (EAN)	4099986189652
Qty.	1 items

**VPU AC II+III 3+1 275/40 S**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Depth	70 mm	Depth (inches)	2.7559 inch
Height	99 mm	Height (inches)	3.8976 inch
Width	36 mm	Width (inches)	1.4173 inch
Net weight	264 g		

**Temperatures**

Storage temperature Operating temperature -40 °C...85 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**Connection data, remote alert**

Connection type Screw connection

**General data**

Optical function display	green = OK; red = arrester is defective - replace	Segment	Power distribution
Design	Installation housing; 2TE, Insta IP 20	UL 94 flammability rating	V-0
Colour	grey	Protection degree	IP20 in installed state
Mounting rail	TS 35	Operating altitude	≤ 2000 m

**Insulation coordination acc. to EN 50178**

Surge voltage category III Pollution severity 2

**Rated data IEC / EN**

Number of poles	4	Combined pulse UOC	6 kV
Signalling contact	No	Rated voltage (AC)	230 V
Low voltage network	TN-S, TT	Protection level Up at IN (N-PE)	≤ 1.5 kV
Voltage type	AC	Temporary surge voltage (over-voltage) - TOV	335 V
Fuse protection	No Fuse necessary ≤100 A gG	Response time / fallback time	≤ 25 ns, <100 ns
Frequency range, max.	60 Hz	Frequency range, min.	50 Hz
Standards	IEC 61643-11, EN 61643-11	Requirements class, acc. to EN 61643-11	T2, T3
Requirements category acc. to IEC 61643-11	Type II, Type III	Max. continuous voltage, Uc (AC)	275 V
Max. continuous voltage, Uc (N-PE)	255 V	Discharge current Imax (8/20µs) N-PE	40 kA
Discharge current In (8/20µs) N-PE	20 kA	Discharge current In (8/20µs) wire-PE	20 kA

## VPU AC II+III 3+1 275/40 S

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

### Technical data

Discharge current I <sub>max</sub> (8/20μs) wire-PE40 kA	Protection level Up at IN (L/N-PE)	≤ 1.5 kV
Short-circuit current rating ISCCR 25 kA	Discharge current (type III)	3 kA
Integrated back-up fuse No	Protection level Up at IN (L-PE) (type III)	≤1 kV
Protection level Up at IN (N-PE) (type III) ≤1 kV		

### Connection data

Stripping length	15 mm	Conductor connection cross-section PE, stranded, max.	35 mm <sup>2</sup>
Conductor connection cross-section PE, solid, max.	35 mm <sup>2</sup>	Wire connection method	Screw connection
Type of connection	Screw connection	Stripping length, rated connection	15 mm
Tightening torque, max.	1.2 Nm	Wire cross-section, solid, min.	2.5 mm <sup>2</sup>
Wire cross-section, solid, max.	10 mm <sup>2</sup>	Wire connection cross section, finely stranded, min.	2.5 mm <sup>2</sup>
Wire connection cross section, finely stranded, max.	6 mm <sup>2</sup>	Connection cross-section, stranded, min.	2.5 mm <sup>2</sup>
Connection cross-section, stranded, max.	10 mm <sup>2</sup>		

### Electrical data

Voltage type	AC
--------------	----

### General data

Number of poles	4	Protection degree	IP20 in installed state
Colour	grey		

### Guarantee

Time interval	5 years
---------------	---------

### Important note


Product information	For use in DC applications, please use the fuse of SIBA Type NH2XL aR/aSF DC 1500 V
---------------------	---

### Classifications

ETIM 8.0	EC000941	ETIM 9.0	EC000941
ETIM 10.0	EC000941	ECLASS 14.0	27-17-12-02
ECLASS 15.0	27-17-12-02		

**Electric symbol**

---



Schematic circuit diagram

---

---

**VPU AC II+III 3+1 275/40 S**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Accessories**

**Crosshead screwdriver Phillips**



VDE insulated crosshead screwdriver, for Phillips screws, SDIK PH DIN 7438, ISO 8764/2-PH, output to ISO 8764-PH, SoftFinish grip

**General ordering data**

Type	SDIK PH0 X 60	Version	
Order No.	<a href="#">2749880000</a>	Screwdriver, Blade width (B): 0 mm, 60 mm, Blade thickness (A): 0	
GTIN (EAN)	4050118897081		
Qty.	1 ST		

**Spare arrester**



**General ordering data**

Type	VPU AC II+III 0 L-N 275...	Version	
Order No.	<a href="#">2907800000</a>	Surge voltage arrester, Low voltage, Spare arrester, TN-S, TT	
GTIN (EAN)	4099986189676		
Qty.	1 ST		
Type	VPU AC II+III 0 L/N-PE ...	Version	
Order No.	<a href="#">2907810000</a>	Surge voltage arrester, Low voltage, Spare arrester, TN-S, TT	
GTIN (EAN)	4099986189683		
Qty.	1 ST		