
Data sheet

# A4C 6 FE DL

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



To feed through power, signal, and data is the classical requirement in electrical engineering and panel building. The insulating material, the connection system and the design of the terminal blocks are the differentiating features. A feed-through terminal block is suitable for joining and/or connecting one or more conductors. They could have one or more connection levels that are on the same potential or insulated against one another.

## General ordering data

| | |
|---|---|
| Version | Feed-through terminal, PUSH IN, 6 mm², 800 V, 41 A, black/yellow |
| Order No. | 2881530000 |
| Type | A4C 6 FE DL |
| GTIN (EAN) | 4064675674214 |
| Qty. | 50 items |
| Delivery status | This article will no longer be available in the future. |
| Last order date | 2027-04-30T00:00:00+02:00 |
| Alternative product | A4C 6 FE |

# A4C 6 FE DL

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Technical data

### Approvals

| | |
|---|---|
| Approvals |  |
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (cURus) | E60693 |

### Dimensions and weights

| | | | |
|---|---|---|---|
| Depth | 45.5 mm | Depth (inches) | 1.7913 inch |
| Height | 102 mm | Height (inches) | 4.0157 inch |
| Width | 8.1 mm | Width (inches) | 0.3189 inch |
| Net weight | 23.28 g | | |

### Temperatures

| | | | |
|---|---|---|---|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -60 °C...85 °C |
| Continuous operating temp., min. | -60 °C | Continuous operating temp., max. | 130 °C |

### Environmental Product Compliance

| | | |
|---|---|---|
| RoHS Compliance Status | Compliant without exemption | |
| REACH SVHC | No SVHC above 0.1 wt% | |
| Product Carbon Footprint | Cradle to gate | 0.637 kg CO2 eq. |

### Material data

| | | | |
|---|---|---|---|
| Basic material | Wemid | Colour | black/yellow |
| Colour of operational elements | orange | UL 94 flammability rating | V-0 |

### Rating data IECEx/ATEX

| | | | |
|---|---|---|---|
| Certificate No. (ATEX) | TUEV16ATEX7909U | Certificate No. (IECEX) | IECEXTUR16.0036U |
| Max. voltage (ATEX) | 550 V | Current (ATEX) | 37 A |
| Wire cross section max. (ATEX) | 6 mm² | Max. voltage (IECEX) | 550 V |
| Current (IECEX) | 37 A | Wire cross section max. (IECEX) | 6 mm² |

### System specifications

| | | | |
|---|---|---|---|
| End cover plate required | Yes | Number of potentials | 1 |
| Number of levels | 1 | Number of clamping points per level | 4 |
| Number of potentials per tier | 1 | Levels cross-connected internally | No |
| Mounting rail | TS 35 | N-function | No |
| PE function | No | PEN function | No |

### Additional technical data

| | | | |
|---|---|---|---|
| Open sides | right | Snap-on | Yes |
| Type of fixing | TS 35 | Explosion-tested version | No |

# A4C 6 FE DL

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Technical data

| | |
|---|---|
| Type of mounting | TS 35 |

### CSA rating data

| | | | |
|---|---|---|---|
| Wire cross section max. (CSA) | 8 AWG | Voltage size C (CSA) | 600 V |
| Current size C (CSA) | 38 A | Certificate No. (CSA) | 227442-80219640 |
| Voltage size D (CSA) | 600 V | Current size D (CSA) | 5 A |
| Wire cross section min. (CSA) | 22 AWG | | |

### Conductors for clamping (additional connection)

| | |
|---|---|
| Connection type, additional connection | PUSH IN |

### Conductors for clamping (rated connection)

| | | | |
|---|---|---|---|
| Gauge to IEC 60947-1 | A5 | | |
| Wire connection cross section AWG, max. | AWG 8 | | |
| Connection direction | top | | |
| Stripping length | 12 mm | | |
| Type of connection | PUSH IN | | |
| Number of connections | 4 | | |
| Clamping range, max. | 10 mm² | | |
| Clamping range, min. | 0.34 mm² | | |
| Blade size | 1.0 x 5.5 mm | | |
| Wire connection cross section AWG, min. | AWG 22 | | |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 6 mm² | | |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.34 mm² | | |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 10 mm² | | |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.34 mm² | | |
| Wire connection cross-section, finely stranded, max. | 10 mm² | | |
| Wire connection cross section, finely stranded, min. | 0.34 mm² | | |
| Connection cross-section, stranded, max. | 6 mm² | | |
| Connection cross-section, stranded, min. | 0.34 mm² | | |
| Twin wire-end ferrules, max. | 1.5 mm² | | |
| Twin wire-end ferrules, min. | 0.5 mm² | | |
| Wire connection cross-section, solid core, max. | 6 mm² | | |
| Wire connection cross-section, solid core, min. | 0.34 mm² | | |
| Connection cross-section, finely stranded (rated connection), min. | 0.34 mm² | | |
| Tube length for wire-end ferrule with plastic collar DIN 46228/4 | Tube length | min. | 10 mm |
| | | max. | 12 mm |
| | Cross-section for conductor connection | min. | 0.5 mm² |
| | | max. | 1 mm² |
| | Tube length | min. | 10 mm |
| | | max. | 18 mm |

Weidmüller

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Technical data

| | | | |
|---|---|---|---|
| | Cross-section for conductor connection | nominal | 1.5 mm² |
| | Tube length | min. | 12 mm |
| | | max. | 18 mm |
| | Cross-section for conductor connection | nominal | 2.5 mm² |
| | Tube length | min. | 10 mm |
| | | max. | 18 mm |
| | Cross-section for conductor connection | min. | 4 mm² |
| | | max. | 6 mm² |
| Tube length for twin wire-end ferrule | Tube length | min. | 10 mm |
| | | max. | 12 mm |
| | Cross-section for conductor connection | nominal | 0.5 mm² |
| | Tube length | min. | 10 mm |
| | | max. | 18 mm |
| | Cross-section for conductor connection | nominal | 0.75 mm² |
| | Tube length | min. | 12 mm |
| | | max. | 18 mm |
| | Cross-section for conductor connection | min. | 1 mm² |
| | | max. | 1.5 mm² |
| Tube length for wire-end ferrule without plastic collar DIN 46228/1 | Tube length | nominal | 10 mm |
| | Cross-section for conductor connection | min. | 0.5 mm² |
| | | max. | 1 mm² |
| | Tube length | min. | 10 mm |
| | Cross-section for conductor connection | min. | 1.5 mm² |
| | | max. | 2.5 mm² |
| | Tube length | min. | 12 mm |
| | | max. | 18 mm |
| | Cross-section for conductor connection | nominal | 4 mm² |
| | Tube length | min. | 10 mm |
| | | max. | 18 mm |
| | Cross-section for conductor connection | min. | 6 mm² |
| | | max. | 10 mm² |

| | | |
|---|---|---|
| Tube length for wire-end ferrule with plastic collar acc. to cross-section | Cross-section, min. | 0.5 mm² |
| | Cross-section, max. | 1 mm² |
| | Tube length, min. | 10 mm |
| | Tube length, max. | 12 mm |
| | Cross-section, min. | 1.5 mm² |
| | Cross-section, max. | 1.5 mm² |
| | Tube length, min. | 10 mm |
| | Tube length, max. | 18 mm |
| | Cross-section, min. | 2.5 mm² |
| | Cross-section, max. | 2.5 mm² |
| | Tube length, min. | 12 mm |
| | Tube length, max. | 18 mm |
| | Cross-section, min. | 4 mm² |
| | Cross-section, max. | 6 mm² |
| | Tube length, min. | 10 mm |
| | Tube length, max. | 18 mm |
| Tube length for wire-end ferrule without plastic collar acc. to cross-section | Cross-section, min. | 0.5 mm² |
| | Cross-section, max. | 1 mm² |
| | Tube length, min. | 10 mm |
| | Tube length, max. | 10 mm |
| | Cross-section, min. | 1.5 mm² |
| | Cross-section, max. | 2.5 mm² |
| | Tube length, min. | 10 mm |
| | Tube length, max. | 18 mm |
| | Cross-section, min. | 4 mm² |
| | Cross-section, max. | 4 mm² |
| | Tube length, min. | 12 mm |

Weidmüller

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

# Technical data

| | | |
|---|---|---|
| | Tube length, max. | 18 mm |
| | Cross-section, min. | 6 mm² |
| | Cross-section, max. | 6 mm² |
| | Tube length, min. | 10 mm |
| | Tube length, max. | 18 mm |
| Tube length for twin wire-end ferrule acc. to cross-section | Cross-section, min. | 0.5 mm² |
| | Cross-section, max. | 0.5 mm² |
| | Tube length, min. | 10 mm |
| | Tube length, max. | 12 mm |
| | Cross-section, min. | 0.75 mm² |
| | Cross-section, max. | 0.75 mm² |
| | Tube length, min. | 10 mm |
| | Tube length, max. | 12 mm |
| | Cross-section, min. | 1 mm² |
| | Cross-section, max. | 1.5 mm² |
| | Tube length, min. | 10 mm |
| | Tube length, max. | 18 mm |

## General

| | | | |
|---|---|---|---|
| Wire connection cross section AWG, max. | AWG 8 | Wire connection cross section AWG, min. | AWG 22 |
| Standards | IEC 60947-7-1 | Mounting rail | TS 35 |

## Rating data

| | | | |
|---|---|---|---|
| Rated cross-section | 6 mm² | Rated voltage | 800 V |
| Rated DC voltage | 800 V | Nominal current | 41 A |
| Current at maximum wires | 41 A | Standards | IEC 60947-7-1 |
| Volume resistance | 0.78 mΩ | Rated impulse withstand voltage | 8 kV |
| Power loss in accordance with IEC 60947-7-x | 1.31 W | Surge voltage category | III |
| Pollution severity | 3 | | |

## UL rating data

| | | | |
|---|---|---|---|
| Conductor size Factory wiring max. (cURus) | 8 AWG | Voltage size B (cURus) | 600 V |
| Voltage size D (cURus) | 600 V | Certificate No. (cURus) | E60693 |
| Conductor size Field wiring min. (cURus) | 22 AWG | Conductor size Factory wiring min. (cURus) | 22 AWG |
| Current size B (cURus) | 38 A | Voltage size C (cURus) | 600 V |
| Current size C (cURus) | 38 A | Current size D (cURus) | 5 A |
| Conductor size Field wiring max. (cURus) | 8 AWG | | |

## Classifications

| | | | |
|---|---|---|---|
| ETIM 8.0 | EC000897 | ETIM 9.0 | EC000897 |
| ETIM 10.0 | EC000897 | ECLASS 14.0 | 27-25-01-01 |
| ECLASS 15.0 | 27-25-01-01 | | |

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Drawings

