

MF 10/7.6 MM WS


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



MultiMark MultiFit

For connectors from competitors.

The elastic surface finish makes for simple installation.

This special material enables the strips to be stretched to accommodate slight variations in spacing, especially with long terminal blocks.

A print resolution of 300 dpi also produces a very legible script. Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence
- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence
- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

General ordering data

| | |
|------------|---|
| Version | Terminal marker, 10 x 7.6 mm, Pitch in mm (P): 7.60 white |
| Order No. | 2885990000 |
| Type | MF 10/7.6 MM WS |
| GTIN (EAN) | 4064675854593 |
| Qty. | 400 items |

MF 10/7.6 MM WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 0.7 mm | Depth (inches) | 0.0276 inch |
| Height | 10 mm | Height (inches) | 0.3937 inch |
| Width | 7.6 mm | Width (inches) | 0.2992 inch |
| Net weight | 0.13 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -50...90 °C |
|-----------------------------|-------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General data

| | | | |
|-----------------------------------|--------------|-----------------------------------|-------------|
| Version | halogen-free | Width | 7.6 mm |
| UL 94 flammability rating | V-2 | Operating temperature range, max. | 90 °C |
| Operating temperature range, min. | -50 °C | Colour | white |
| Halogen | No | Basic material | PC-ABS, TPU |
| Printed characters | neutral | Operating temperature range | -50...90 °C |

Connector markers

| | |
|-----------------|---------|
| Pitch in mm (P) | 7.60 mm |
|-----------------|---------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000761 | ETIM 7.0 | EC000761 |
| ETIM 8.0 | EC000761 | ETIM 9.0 | EC000761 |
| ETIM 10.0 | EC000761 | ECLASS 9.0 | 27-14-11-37 |
| ECLASS 9.1 | 27-14-11-37 | ECLASS 10.0 | 27-14-11-37 |
| ECLASS 11.0 | 27-28-11-01 | ECLASS 12.0 | 27-28-11-01 |
| ECLASS 13.0 | 27-28-11-01 | ECLASS 14.0 | 27-28-11-01 |
| ECLASS 15.0 | 27-28-11-01 | | |

Drawings



MF 10/7.6 MM WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Ink ribbons




These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | | |
|------------|----------------------------|------------|--|
| Type | RIBBON MM-TB 25/360 SW | Version | |
| Order No. | 2005090000 | Ink ribbon | |
| GTIN (EAN) | 4050118390216 | | |
| Qty. | 1 ST | | |

THM MULTIMARK




These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | | |
|------------|----------------------------|---------|--|
| Type | MULTIMARK ROLLER MF | Version | |
| Order No. | 2518600000 | | |
| GTIN (EAN) | 4050118531305 | | |
| Qty. | 1 ST | | |

THM MULTIMARK PLUS



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | | |
|------------|----------------------------|---------|--|
| Type | MULTIMARK PLUS ROLLER MF | Version | |
| Order No. | 2661610000 | | |
| GTIN (EAN) | 4050118681222 | | |
| Qty. | 1 ST | | |