

ACT20D-LCD-CI-ILP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Suitable for field mounting to display an analog 4- 20 mA signal.

The digital indicator is looped into the current loop.

Features:

- No separate supply voltage is required.
- For industrial environments, mounted in the control cabinet door, the protection class is IP65.
- Even in unfavourable lighting conditions, the display value is clearly visible.
- HART®-transparent
- Adjustable scaling of the display

General ordering data

Version	Display, Input : 4-20 mA, (loop powered), HART® transparency, Output : Display
Order No.	2920000000
Type	ACT20D-LCD-CI-ILP
GTIN (EAN)	4099986580336
Qty.	1 items

ACT20D-LCD-CI-ILP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	120 mm	Depth (inches)	4.7244 inch
Height	48 mm	Height (inches)	1.8898 inch
Width	96 mm	Width (inches)	3.7795 inch
Net weight	262 g		

Temperatures

Storage temperature	-20 °C...60 °C	Operating temperature	-20 °C...60 °C
Humidity	0...95 % (no condensation)		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	f4905d12-f516-4eb5-90a8-8c87685bc956

Display

Display range	-9999...9999	Display value	Current
Type	4-character, LCD display, 16 mm	Decimal point	18888, 1.8888, 18.888, 188.88, 1888.8
Scaling	Variable	Dimmable	Yes
Adjustment of display backlighting	0%, 50%, 100%		

General data

Type of connection	Tension clamp connection with actuator	Accuracy	<0.1 % of measuring range
Type of mounting	Frontpanel mounting, Front mounting	Protection degree	IP65
DIN Rail compatibility	No	Supply voltage	Loop powered, via 4...20 mA input
Step response time	≤1s	Temperature coefficient	≤ 0.01 °C of measuring range / °C
Configuration	Front push-button, DIP switch to lock / unlock the front push-button	HART® transparency supported	Yes

Input

Sensor	Current source, 4- wire sensor (with own power supply)	Number inputs	1
Input measurement range	3.6 ... 23 mA (NAMUR NE43 conform)	Input current	4...20mA

ACT20D-LCD-CI-ILP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Type of signal forwarding according to HART®	unchanged	Response time	≤ 1 s
HART® transparency supported	Yes	Voltage drop, current input	without backlight <1.5 V @ 20 mA, half backlight <6.5 V @ 20 mA, full backlight <10.5 V @ 20 mA

Connection data

Wire connection method	Screw connection	Type of connection	Tension clamp connection with actuator
Wire connection cross section AWG, min.	AWG 26	Wire connection cross section AWG, max.	AWG 14
Wire connection cross section, finely stranded, min.	0.13 mm ²	Wire connection cross section, finely stranded, max.	2.08 mm ²

Classifications

ETIM 8.0	EC000677	ETIM 9.0	EC000677
ETIM 10.0	EC000677	ECLASS 14.0	27-14-31-10
ECLASS 15.0	27-14-31-10		


ACT20D-LCD-CI-ILP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany


www.weidmueller.com

Drawings


Dimensioned drawing



Wiring diagram



Menu



setting