


## LLFS 7.50/05/90V 5.0SN BK BX SO

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

### Product image



The sturdy, direct connection for extreme current and voltage requirements in all power electronics applications such as solar inverters, frequency converters, servo-controllers and power supplies.

### General ordering data

|              |  |
|--------------|--|
| Version      | Printed circuit board terminals, 7.50 mm, Number of poles: 5, 90°, Solder pin length (l): 5 mm, tinned, black, PUSH IN without actuator, Clamping range, max. : 6 mm², Box |
| Order No.    | <a href="#">2891910000</a>   |
| Type         | LLFS 7.50/05/90V 5.0SN BK BX SO  |
| GTIN (EAN)   | 4064675881483  |
| Qty.         | 50 items   |
| Product data | IEC: 1000 V / 41 A / 0.5 - 6 mm²<br>UL: 600 V / 37 A / AWG 24 - AWG 8  |
| Packaging    | Box  |

## LLFS 7.50/05/90V 5.0SN BK BX SO

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|                          |             |                 |             |
|--------------------------|-------------|-----------------|-------------|
| Depth                    | 20.05 mm    | Depth (inches)  | 0.7894 inch |
| Height                   | 30.56 mm    | Height (inches) | 1.2031 inch |
| Height of lowest version | 25.56 mm    | Width           | 38.5 mm     |
| Width (inches)           | 1.5157 inch | Net weight      | 19.48 g     |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## System parameters

|  |                            |  |                               |
|--|----------------------------|--|-------------------------------|
| Product family                             | OMNIMATE Power - series LL | Wire connection method                     | PUSH IN without actuator      |
| Mounting onto the PCB                      | THT solder connection      | Conductor outlet direction                 | 90°                           |
| Pitch in mm (P)                            | 7.50 mm                    | Pitch in inches (P)                        | 0.295 "                       |
| Number of poles                            | 5                          | Pin series quantity                        | 1                             |
| Fitted by customer                         | No                         | Number of rows                             | 1                             |
| Solder pin length (l)                      | 5 mm                       | Solder pin dimensions                      | d = 1.5 mm                    |
| Solder eyelet hole diameter (D)            | 2 mm                       | Solder eyelet hole diameter tolerance (D)+ | 0,1 mm                        |
| Touch-safe protection acc. to DIN VDE 0470 | IP 20                      | Touch-safe protection acc. to DIN VDE      | Safe from finger touch 57 106 |
| Protection degree                          | IP20                       |  |                               |

## Material data

|                                |            |                                      |                   |
|--------------------------------|------------|--------------------------------------|-------------------|
| Insulating material            | Wemid (PA) | Colour                               | black             |
| Colour of operational elements | orange     | Colour chart (similar)               | RAL 9011          |
| Insulating material group      | I          | Moisture Level (MSL)                 |                   |
| UL 94 flammability rating      | V-0        | Contact material                     | Cu-alloy          |
| Contact surface                | tinned     | Layer structure of solder connection | 4...10 µm Sn matt |
| Storage temperature, min.      | -40 °C     | Storage temperature, max.            | 70 °C             |
| Operating temperature, min.    | -40 °C     | Operating temperature, max.          | 120 °C            |

## Conductors suitable for connection

|  |  |      |            |
|--|--|------|------------|
| Clamping range, min.   | 0.25 mm <sup>2</sup>                   |      |            |
| Clamping range, max.   | 6 mm <sup>2</sup>                      |      |            |
| Solid, min. H05(07) V-U  | 0.5 mm <sup>2</sup>                    |      |            |
| Solid, max. H05(07) V-U  | 6 mm <sup>2</sup>                      |      |            |
| Stranded, min. H07V-R  | 0.5 mm <sup>2</sup>                    |      |            |
| Flexible, min. H05(07) V-K   | 0.5 mm <sup>2</sup>                    |      |            |
| Flexible, max. H05(07) V-K   | 6 mm <sup>2</sup>                      |      |            |
| w. plastic collar ferrule, DIN 46228 pt 4, 0.25 mm <sup>2</sup> min. |  |      |            |
| w. plastic collar ferrule, DIN 46228 pt 4, 6 mm <sup>2</sup> max.    |  |      |            |
| w. wire end ferrule, DIN 46228 pt 1, min.                            | 0.25 mm <sup>2</sup>                   |      |            |
| w. wire end ferrule, DIN 46228 pt 1, max.                            | 6 mm <sup>2</sup>                      |      |            |
| Clampable conductor  | Cross-section for conductor connection | Type | fine-wired |

**LLFS 7.50/05/90V 5.0SN BK BX SO**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

|  |                              |                             |
|--|------------------------------|-----------------------------|
|  | nominal                      | 0.5 mm <sup>2</sup>         |
| wire end ferrule                       | Stripping length             | nominal 14 mm               |
|  | Recommended wire-end ferrule | <a href="#">H0.5/18 OR</a>  |
| Cross-section for conductor connection | Type                         | fine-wired                  |
|  | nominal                      | 1 mm <sup>2</sup>           |
| wire end ferrule                       | Stripping length             | nominal 15 mm               |
|  | Recommended wire-end ferrule | <a href="#">H1.0/18 GE</a>  |
| Cross-section for conductor connection | Type                         | fine-wired                  |
|  | nominal                      | 1.5 mm <sup>2</sup>         |
| wire end ferrule                       | Stripping length             | nominal 15 mm               |
|  | Recommended wire-end ferrule | <a href="#">H1.5/18D SW</a> |
|  | Stripping length             | nominal 12 mm               |
|  | Recommended wire-end ferrule | <a href="#">H1.5/12</a>     |
| Cross-section for conductor connection | Type                         | fine-wired                  |
|  | nominal                      | 0.75 mm <sup>2</sup>        |
| wire end ferrule                       | Stripping length             | nominal 14 mm               |
|  | Recommended wire-end ferrule | <a href="#">H0.75/18 W</a>  |
| Cross-section for conductor connection | Type                         | fine-wired                  |
|  | nominal                      | 2.5 mm <sup>2</sup>         |
| wire end ferrule                       | Stripping length             | nominal 14 mm               |
|  | Recommended wire-end ferrule | <a href="#">H2.5/19D BL</a> |
|  | Stripping length             | nominal 12 mm               |
|  | Recommended wire-end ferrule | <a href="#">H2.5/12</a>     |
| Cross-section for conductor connection | Type                         | fine-wired                  |
|  | nominal                      | 4 mm <sup>2</sup>           |
| wire end ferrule                       | Stripping length             | nominal 12 mm               |
|  | Recommended wire-end ferrule | <a href="#">H4.0/12</a>     |
|  | Stripping length             | nominal 14 mm               |
|  | Recommended wire-end ferrule | <a href="#">H4.0/20D GR</a> |
| Cross-section for conductor connection | Type                         | fine-wired                  |
|  | nominal                      | 6 mm <sup>2</sup>           |
| wire end ferrule                       | Stripping length             | nominal 14 mm               |
|  | Recommended wire-end ferrule | <a href="#">H6.0/20 SW</a>  |
|  | Stripping length             | nominal 12 mm               |
|  | Recommended wire-end ferrule | <a href="#">H6.0/12</a>     |

Reference text Length of ferrules is to be chosen depending on the product and the rated voltage.. The outside diameter of the plastic collar should not be larger than the pitch (P)

**Rated data acc. to IEC**

|  |                                  |  |        |
|--|----------------------------------|--|--------|
| tested acc. to standard  | In accordance with IEC 60947-7-1 | Rated current, min. number of poles (Tu=20°C)                  | 41 A   |
| Rated current, max. number of poles (Tu=20°C)                  | 34 A                             | Rated current, min. number of poles (Tu=40°C)                  | 37 A   |
| Rated current, max. number of poles (Tu=40°C)                  | 29 A                             | Rated voltage for surge voltage class / pollution degree II/2  | 1000 V |
| Rated voltage for surge voltage class / pollution degree III/2 | 1000 V                           | Rated voltage for surge voltage class / pollution degree III/3 | 1000 V |

## LLFS 7.50/05/90V 5.0SN BK BX SO

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

### Technical data

Rated impulse voltage for surge voltage class/ pollution degree II/2 8 kV

Rated impulse voltage for surge voltage class/ contamination degree III/3 8 kV

Rated impulse voltage for surge voltage class/ pollution degree III/2 8 kV

#### Rated data acc. to CSA

Rated voltage (Use group B / CSA) 600 V

Rated voltage (Use group D / CSA) 600 V

Rated current (Use group C / CSA) 37 A

Wire cross-section, AWG, min. AWG 24

Rated voltage (Use group C / CSA) 600 V

Rated current (Use group B / CSA) 37 A

Rated current (Use group D / CSA) 5 A

Wire cross-section, AWG, max. AWG 8

#### Rated data acc. to UL 1059

Rated voltage (Use group B / UL 1059) 600 V

Rated voltage (Use group D / UL 1059) 600 V

Rated current (Use group C / UL 1059) 37 A

Wire cross-section, AWG, min. AWG 24

Rated voltage (Use group C / UL 1059) 600 V

Rated current (Use group B / UL 1059) 37 A

Rated current (Use group D / UL 1059) 5 A

Wire cross-section, AWG, max. AWG 8

#### Packing

Packaging Box VPE length 218.00 mm

VPE width 213.00 mm VPE height 48.00 mm

#### Type tests

|                               |                |  |                              |  |
|-------------------------------|----------------|--|------------------------------|--|
| Test: Durability of markings  | Standard       | IEC 60947-7-4 section 7.1.4 / 08.13  |                              |  |
|                               | Test           | mark of origin, type identification, type of material, pitch, durability, stripping length |                              |  |
|                               | Evaluation     | available  |                              |  |
| Test: Clampable cross section | Standard       | IEC 60999-1 section 7 and 9.1 / 11.99, IEC 60947-1 section 8.2.4.5.1 / 03.11               |                              |  |
|                               | Conductor type | Type of conductor and conductor cross-section  | solid 0.5 mm <sup>2</sup>    |  |
|                               |                | Type of conductor and conductor cross-section  | stranded 0.5 mm <sup>2</sup> |  |
|                               |                | Type of conductor and conductor cross-section  | solid 6 mm <sup>2</sup>      |  |
|                               |                | Type of conductor and conductor cross-section  | stranded 6 mm <sup>2</sup>   |  |
|                               |                | Type of conductor and conductor cross-section  | AWG 24/19                    |  |
|                               |                | Type of conductor and conductor cross-section  | AWG 24/1                     |  |
|                               |                | Type of conductor and conductor cross-section  | AWG 10/1                     |  |
|                               |                | Type of conductor and conductor cross-section  | AWG 10/19                    |  |
|                               |                | Type of conductor and conductor cross-section  | H07V-K10                     |  |
| Evaluation                    | passed         |  |                              |  |

**LLFS 7.50/05/90V 5.0SN BK BX SO**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

|   |   |  |           |  |
|---|---|--|-----------|--|
| Test for damage to and accidental loosening of conductors | Standard                                      | IEC 60999-1 section 9.4 / 11.99, IEC 60999-1 section 9.5 / 11.99 |           |  |
|   | Requirement                                   | 0.3 kg   |           |  |
|   | Conductor type                                | Type of conductor and conductor cross-section                    | H05V-K0.5 |  |
|   |   | Type of conductor and conductor cross-section                    | H05V-U0.5 |  |
|   | Evaluation                                    | passed   |           |  |
|   | Requirement                                   | 0,4 kg   |           |  |
|   | Conductor type                                | Type of conductor and conductor cross-section                    | H07V-K1   |  |
|   |   | Type of conductor and conductor cross-section                    | H07V-U1   |  |
|   | Evaluation                                    | passed   |           |  |
|   | Requirement                                   | 0.7 kg   |           |  |
|   | Conductor type                                | Type of conductor and conductor cross-section                    | H07V-K2.5 |  |
|   |   | Type of conductor and conductor cross-section                    | H07V-U2.5 |  |
|   | Evaluation                                    | passed   |           |  |
|   | Requirement                                   | 0.9 kg   |           |  |
|   | Conductor type                                | Type of conductor and conductor cross-section                    | H07V-K4   |  |
| Type of conductor and conductor cross-section             |   | H07V-U4.0  |           |  |
| Evaluation  | passed  |  |           |  |
| Requirement   | 1.4 kg  |  |           |  |
| Conductor type  | Type of conductor and conductor cross-section | H07V-K6  |           |  |
|   | Type of conductor and conductor cross-section | H07V-U6  |           |  |
| Evaluation  | passed  |  |           |  |
| Pull-out test   | Standard                                      | DIN EN 60999-1 section 9.5 / 12.00                               |           |  |
|   | Requirement                                   | ≥20 N  |           |  |
|   | Conductor type                                | Type of conductor and conductor cross-section                    | H05V-K0.5 |  |
|   |   | Type of conductor and conductor cross-section                    | H05V-U0.5 |  |
|   | Evaluation                                    | passed   |           |  |
|   | Requirement                                   | ≥50 N  |           |  |
|   | Conductor type                                | Type of conductor and conductor cross-section                    | H07V-K2.5 |  |
|   |   | Type of conductor and conductor cross-section                    | H07V-U2.5 |  |
|   | Evaluation                                    | passed   |           |  |
|   | Requirement                                   | ≥60 N  |           |  |
| Conductor type  | Type of conductor and conductor cross-section | H07V-K4  |           |  |

**LLFS 7.50/05/90V 5.0SN BK BX SO**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

|                |   |           |
|----------------|---|-----------|
|                | Type of conductor and conductor cross-section | H07V-U4.0 |
| Evaluation     | passed  |           |
| Requirement    | ≥80 N   |           |
| Conductor type | Type of conductor and conductor cross-section | H07V-K6   |
|                | Type of conductor and conductor cross-section | H07V-U6   |
| Evaluation     | passed  |           |
| Requirement    | ≥35 N   |           |
| Conductor type | Type of conductor and conductor cross-section | H07V-K1   |
|                | Type of conductor and conductor cross-section | H07V-U1   |
| Evaluation     | passed  |           |

**Important note**

|                |   |
|----------------|---|
| IPC conformity | Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.  |
| Notes          | <ul style="list-style-type: none"> <li>• Additional variants on request</li> <li>• Rated current related to rated cross-section &amp; min. No. of poles.</li> <li>• Wire end ferrule without plastic collar to DIN 46228/1</li> <li>• Wire end ferrule with plastic collar to DIN 46228/4</li> <li>• P on drawing = pitch</li> <li>• Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.</li> <li>• The test point can only be used as potential-pickup point.</li> <li>• The single-position PCB terminal block can be used for voltages up to 1500 V (DC) and 1000 V (AC). The relevant device standard and the appropriate required clearances and creepage distances should be observed in the application</li> <li>• Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months</li> </ul> |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002643    | ETIM 9.0    | EC002643    |
| ETIM 10.0   | EC002643    | ECLASS 14.0 | 27-46-01-01 |
| ECLASS 15.0 | 27-46-01-01 |             |             |


LLFS 7.50/05/90V 5.0SN BK BX SO

Weidmüller Interface GmbH & Co. KG  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany


www.weidmueller.com

Drawings

Product image



Dimensional drawing



Derating curve



Derating curve



Product benefits



Power up to UL 600 V offset solder pins

Product benefits



Tool-free wiring Top contact security

## LLFS 7.50/05/90V 5.0SN BK BX SO

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Slotted screwdriver



VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

#### General ordering data

|            |                            |                          |  |
|------------|----------------------------|--------------------------|--|
| Type       | SDIS 0.5X3.0X100           | Version                  |  |
| Order No.  | <a href="#">9008380000</a> | Screwdriver, Screwdriver |  |
| GTIN (EAN) | 4032248056347              |                          |  |
| Qty.       | 1 ST                       |                          |  |
| Type       | SDS 0.5X3.0X80             | Version                  |  |
| Order No.  | <a href="#">9008320000</a> | Screwdriver, Screwdriver |  |
| GTIN (EAN) | 4032248056262              |                          |  |
| Qty.       | 1 ST                       |                          |  |

### Additional accessories



No task is too small when creating the perfect solution. Connections form just one part of the overall process. Small details are often the key to the perfect solution in applications where potentials are tested, grouped or even isolated.

A system is not a system without small but essential details:

- Test plugs ensure reliable pick-up from diagnostic sockets

In tandem with the manufacturing process and application.

#### General ordering data

|            |                            |  |   |
|------------|----------------------------|--|---|
| Type       | PS 2.0 MC                  | Version  |   |
| Order No.  | <a href="#">0310000000</a> | PCB plug-in connector, Accessories, Test plug, red, Number of poles: |   |
| GTIN (EAN) | 4008190000059              |  | 1 |
| Qty.       | 20 ST                      |  |   |

## LLFS 7.50/05/90V 5.0SN BK BX SO

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Tools



- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

### General ordering data

|            |                            |                                   |  |
|------------|----------------------------|-----------------------------------|--|
| Type       | STRIPAX                    | Version                           |  |
| Order No.  | <a href="#">9005000000</a> | Tools, Stripping and cutting tool |  |
| GTIN (EAN) | 4008190072506              |                                   |  |
| Qty.       | 1 ST                       |                                   |  |