

UV66-ADV-10-CAP-W-V2**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



u-view Advanced touch panels from Weidmüller offer excellent image quality and can be used in most industrial environments. The portfolio features various screen sizes from 7" to 21.5" and has high-resolution capacitive touchscreens with support for swipe gestures and glove operation. All panels are equipped with a Linux operating system and an HTML5-capable browser and are optimised for web applications through the integrated kiosk mode and their simple configuration. As a result, they are the perfect solution for web-based visualisations and enable access to a variety of web servers, such as u-OS, u-create PROCON-WEB, u-control web and many more. The panels have a particularly flat design, with an industrial IP66 housing.

General ordering data

| | |
|---------------------|---|
| Order No. | 2933040000 |
| Type | UV66-ADV-10-CAP-W-V2 |
| GTIN (EAN) | 4099986674455 |
| Qty. | 1 items |
| Delivery status | This article will no longer be available in the future. |
| Available until | 2025-12-09T00:00:00+01:00 |
| Alternative product | UV66-ADV-10-CAP-W-V2 |

UV66-ADV-10-CAP-W-V2

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E230683

Dimensions and weights

| | | | |
|------------|----------|-----------------|--------------|
| Depth | 52 mm | Depth (inches) | 2.0472 inch |
| Height | 202.3 mm | Height (inches) | 7.9646 inch |
| Width | 283.1 mm | Width (inches) | 11.1456 inch |
| Net weight | 2340 g | | |

Temperatures

| | | | |
|---------------------|--|-----------------------|------------------|
| Storage temperature | -30 °C ... +70 °C | Operating temperature | -20 °C ... 60 °C |
| Humidity | 95% relative humidity, non-condensing @ 40°C | | |

Environmental Product Compliance

| | | | |
|--------------------------------------|---|--|--|
| RoHS Compliance Status | Compliant with exemption | | |
| RoHS Exemption (if applicable/known) | 6c, 7a, 7cl | | |
| REACH SVHC | Lead 7439-92-1, 1, 2-dimethoxyethane; ethylene glycol dimethyl ether (EGDME) 110-71-4 | | |

Equipment

| | | | |
|-------------------------------|------------------------------|------------------|-----------------------|
| Size | 10.1" | Resolution | 1280 x 800 |
| Number of displayable colours | 16000000 | Luminance | 500 cd/m ² |
| Touch-Screen | Projected capacitive (P-CAP) | Material display | Glass |
| Material frame | Aluminium coated | | |

General data

| | | | |
|----------------------|---------------------------------|--------|--|
| Protection degree | Built-in: IP66, Enclosure: IP20 | | |
| Operating system | Linux Yocto 4.0. | | |
| Voltage supply range | Voltage type | DC | |
| | Voltage, min. | 19.2 V | |
| | Voltage, max. | 28.8 V | |
| Voltage supply | 24 V DC | | |
| Power consumption | Power consumption, nominal | 16.3 W | |
| | Power consumption, max. | 19.9 W | |

System data

| | | | |
|--------------|------------------------------------|-------------------|--|
| Memory (RAM) | 4 GB | Operating system | Linux Yocto 4.0. |
| Memory | 16 MB | Interfaces behind | 2x USB 2.0, 2 x Ethernet 10/100/1000 MBit/s (RJ45) |
| Processor | NXP® ARM® Cortex™-A53 i.MX 8M Mini | Memory (Flash) | 16 GB |

UV66-ADV-10-CAP-W-V2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001412 | ETIM 9.0 | EC001412 |
| ETIM 10.0 | EC001412 | ECLASS 14.0 | 27-33-02-01 |
| ECLASS 15.0 | 27-33-02-01 | | |


UV66-ADV-10-CAP-W-V2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Drawings


www.weidmueller.com

Maße (mm) / Dimensions (mm)



| | LCD | A | B | C | D | E |
|----------------------|-------|-------|-------|----|----|---|
| UV66-ADV-7-CAP-W-V2 | 7" | 205 | 146,9 | 25 | 52 | 7 |
| UV66-ADV-10-CAP-W-V2 | 10.1" | 283,1 | 202,3 | 25 | 52 | 7 |
| UV66-ADV-15-CAP-W-V2 | 15.6" | 419,7 | 269 | 25 | 52 | 7 |
| UV66-ADV-21-CAP-W-V2 | 21.5" | 558,4 | 349,8 | 25 | 52 | 7 |

Montageausschnitt / Panel cut-out



| | LCD | F (mm) | G (mm) | R (mm) |
|----------------------|-------|--------|--------|--------|
| UV66-ADV-7-CAP-W-V2 | 7" | 192,4 | 139 | 5 |
| UV66-ADV-10-CAP-W-V2 | 10.1" | 274,1 | 193,3 | 5 |
| UV66-ADV-15-CAP-W-V2 | 15.6" | 411,9 | 261,2 | 5 |
| UV66-ADV-21-CAP-W-V2 | 21.5" | 549,8 | 341,3 | 5 |

u-view ECO, BASIC and ADVANCED

