

TERMSERIES-COMPACT PROMO

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Using the all-rounder in a small space

TERMSERIES-compact - universal relay with maximum vibration resistance

- Extremely compact with only 6 mm width and 63 mm depth
- 100 % vibration-proof thanks to enclosed design
- Simplified function check thanks to integrated status LED
- Particularly tamper-proof thanks to permanently installed relays

General ordering data

Version	TERMSERIES-compact, Number of contacts: 1, CO contact AgNi, PUSH IN
Order No.	2899000000
Type	TERMSERIES-COMPACT PROMO
GTIN (EAN)	4064675905660
Qty.	10 items

TERMSERIES-COMPACT PROMO

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	62.5 mm	Depth (inches)	2.4606 inch
Height	89.4 mm	Height (inches)	3.5197 inch
Width	6.4 mm	Width (inches)	0.252 inch
Net weight	28.19 g		

Temperatures

Storage temperature	Ambient temperature	-40 °C...60 °C
Operating temperature		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	9e2cbc49-76d9-4611-b8ec-5b4f549a0aa9

Load side

Contact type	1 CO contact (AgNi)
--------------	---------------------

General data

Colour	black
--------	-------

Connection data

Wire connection method	PUSH IN	Stripping length, rated connection	9 mm
Wire cross-section, solid, min.	0.14 mm ²	Wire cross-section, solid, max.	1.5 mm ²
Wire connection cross section, finely stranded, min.	0.14 mm ²	Wire connection cross section, finely stranded, max.	2.5 mm ²
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	0.14 mm ²	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max.	1.5 mm ²

Classifications

ETIM 8.0	EC001437	ETIM 9.0	EC001437
ETIM 10.0	EC001437	ECLASS 14.0	27-37-16-01
ECLASS 15.0	27-37-16-01		