

**WIL-LXXXX-RXPS-5700-X715-M12D-X0**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Our L-series, as standard and premium variants, is the ideal surface mounted light for the industrial field. The swiveling mounting brackets allow for easy and direct mounting and positioning of the illumination field. With only one power supply, it is possible to connect several lights in series. Simple connection technology with circular connectors enables plug-and-play. A special safety glass protects against industrial influences and at the same time provides homogeneous illumination in the light color 5.700K.

**General ordering data**

Order No.	2899380000
Type	<a href="#">WIL-LXXXX-RXPS-5700-X715-M12D-X0</a>
GTIN (EAN)	4064675906438
Qty.	1 items

**WIL-LXXXX-RXPS-5700-X715-M12D-X0**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**
**Approvals**

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E354496

**Dimensions and weights**

Depth	40 mm	Depth (inches)	1.5748 inch
Height	42 mm	Height (inches)	1.6535 inch
Width	715 mm	Width (inches)	28.1496 inch
Net weight	1019 g		

**Temperatures**

Operating temperature -20 - 45°C

**Environmental Product Compliance**

RoHS Compliance Status Compliant with exemption

RoHS Exemption (if applicable/known) 6c

REACH SVHC Lead 7439-92-1

SCIP b1b97d04-507a-4265-bbfb-4e884ff5d5a9

**Cable technical specifications**

Housing main material hard anodised aluminium

**Connection data**

LED Modul is attachable	yes	Number of attachable LED modules, max.	4 piece
Version	pin, straight - socket, straight	Number of poles	5
Coding	A-coded	Connection thread	M12 / M12
Tightening torque	0.8 Nm	Wiring	Pin 1: control white LED 24V DC, Pin 2: NC, Pin 3: GND(-), Pin 4: NC, Pin 5: NC

**Electric data**

Rated voltage	24 V DC	Rated current	762.5 mA
Power	18.3 W	Dimmable	Yes

**General technical data**

Type of connection	Pin connector, Socket connector	Electronic equipment on rolling stock	No
Shape of the LED module	Round	Light colour (CCT)	5700K, White
Light current	1869 lm	Emitting angle	100 °
Illumination level	667 lux	Operating life	60.000 h

## WIL-LXXXX-RXPS-5700-X715-M12D-X0

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

Type of mounting	Screw mounting	Drill hole spacing	745 mm
Protection degree	IP67	Efficiency class (according to EU Directive No. 874/2012)	Not required

### Material data

Material of LED cover	ESG	Housing main material	hard anodised aluminium
-----------------------	-----	-----------------------	-------------------------

### Classifications

ETIM 8.0	EC000996	ETIM 9.0	EC000996
ETIM 10.0	EC000996	ECLASS 14.0	27-11-06-35
ECLASS 15.0	27-11-06-35		

**Dimensioned drawing**



**Pole scheme**



**Pole scheme**



## WIL-LXXXX-RXPS-5700-X715-M12D-X0

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Screw terminal connector



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.

The screw connection can be used in a wide range of applications. With this technology the conductor, optionally with wire-end ferrules, can be plugged into connection elements and secured with a screw. It is the classic, cheapest form of connection technology that also supports multi-conductor connections.

### General ordering data

Type	SAIBGS-P-5A-4/6-M12	Version
Order No.	<a href="#">9457250000</a>	Field attachable connector, M12
GTIN (EAN)	4032248155774	
Qty.	1 ST	
Type	SAISGS-P-5A-4/6-M12	Version
Order No.	<a href="#">9456940000</a>	Field attachable connector, M12
GTIN (EAN)	4008190304935	
Qty.	1 ST	

### PUR halogen-free black (U)



Sensor/actuator cables are used for wiring sensors and actuators and for transmitting data or power in various applications. The moulded cable offers connected and tested connection of the plug-in connector to the cable ex-works. The cables may be exposed to a wide range of conditions, such as humidity, dust, heat, cold, shock or vibration.

Our developers have focused specifically on this issue and designed a host of different M8 and M12 sensor-actuator cables so you are bound to find the solution you need for your application.

Is there something you have not managed to find or you feel needs explanation? Talk to us!

### General ordering data

Type	SAIL-M12BG-5-1.5U	Version
Order No.	<a href="#">9457910150</a>	Sensor/actuator line, One end without connector, M12, Number of poles : 5, 1.5 m, Female socket, straight, Shielded: No, LED: No, Sheath material: PUR, Halogen: No
GTIN (EAN)	4032248528875	
Qty.	1 ST	
Type	SAIL-M12BG-5-3.0U	Version
Order No.	<a href="#">9457910300</a>	Sensor/actuator line, One end without connector, M12, Number of poles : 5, 3 m, Female socket, straight, Shielded: No, LED: No, Sheath material: PUR, Halogen: No
GTIN (EAN)	4032248228843	
Qty.	1 ST	
Type	SAIL-M12BG-5-5.0U	Version
Order No.	<a href="#">9457910500</a>	Sensor/actuator line, One end without connector, M12, Number of poles : 5, 5 m, Female socket, straight, Shielded: No, LED: No, Sheath material: PUR, Halogen: No
GTIN (EAN)	4032248228850	
Qty.	1 ST	

## WIL-LXXXX-RXPS-5700-X715-M12D-X0

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

### Accessories

Type	SAIL-M12BG-5-10U	Version
Order No.	<a href="#">9457911000</a>	Sensor/actuator line, One end without connector, M12, Number of poles : 5, 10 m, Female socket, straight, Shielded: No, LED: No, Sheath material: PUR, Halogen: No
GTIN (EAN)	4032248228867	
Qty.	1 ST	
Type	SAIL-M12G-5-1.0U	Version
Order No.	<a href="#">9457610100</a>	Sensor/actuator line, One end without connector, M12, Number of poles : 5, 1 m, pin, straight, Shielded: No, LED: No, Sheath material: PUR, Halogen: No
GTIN (EAN)	4032248815043	
Qty.	1 ST	
Type	SAIL-M12G-5-3.0U	Version
Order No.	<a href="#">9457610300</a>	Sensor/actuator line, One end without connector, M12, Number of poles : 5, 3 m, pin, straight, Shielded: No, LED: No, Sheath material: PUR, Halogen: No
GTIN (EAN)	4032248230228	
Qty.	1 ST	
Type	SAIL-M12G-5-5.0U	Version
Order No.	<a href="#">9457610500</a>	Sensor/actuator line, One end without connector, M12, Number of poles : 5, 5 m, pin, straight, Shielded: No, LED: No, Sheath material: PUR, Halogen: No
GTIN (EAN)	4032248230235	
Qty.	1 ST	
Type	SAIL-M12G-5-10U	Version
Order No.	<a href="#">9457611000</a>	Sensor/actuator line, One end without connector, M12, Number of poles : 5, 10 m, pin, straight, Shielded: No, LED: No, Sheath material: PUR, Halogen: No
GTIN (EAN)	4032248230242	
Qty.	1 ST	
Type	SAIL-M12GM12G-5-1.0U	Version
Order No.	<a href="#">9457340100</a>	Sensor/actuator line, Connecting line, M12 / M12, Number of poles : 5, 1 m, pin, straight - socket, straight, Shielded: No, LED: No, Sheath material: PUR, Halogen: No
GTIN (EAN)	4032248832583	
Qty.	1 ST	
Type	SAIL-M12GM12G-5-2.0U	Version
Order No.	<a href="#">9457340200</a>	Sensor/actuator line, Connecting line, M12 / M12, Number of poles : 5, 2 m, pin, straight - socket, straight, Shielded: No, LED: No, Sheath material: PUR, Halogen: No
GTIN (EAN)	4008190311285	
Qty.	1 ST	
Type	SAIL-M12GM12G-5-3.0U	Version
Order No.	<a href="#">9457340300</a>	Sensor/actuator line, Connecting line, M12 / M12, Number of poles : 5, 3 m, pin, straight - socket, straight, Shielded: No, LED: No, Sheath material: PUR, Halogen: No
GTIN (EAN)	4008190311896	
Qty.	1 ST	