


V-ZPA FUSE HOLDER**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Order No.	2904480000
Type	V-ZPA FUSE HOLDER
GTIN (EAN)	4099986010383
Qty.	1 items
Delivery status	Discontinued
Available until	2024-07-23T00:00:00+02:00
Alternative product	V-ZPA FUSE HOLDER E

V-ZPA FUSE HOLDER

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	65.5 mm	Depth (inches)	2.5787 inch
Height	95.2 mm	Height (inches)	3.748 inch
Width	18.5 mm	Width (inches)	0.7283 inch
Net weight	144 g		

Temperatures

Storage temperature		Operating temperature	-25 °C...55 °C
Humidity	5 - 95% rel. humidity		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Optical function display	No	Design	Adapter plug
Colour	grey	Protection degree	IP00
Mounting rail	Busbar	Acoustic signal	No
Operating altitude	≤ 4000 m		

Insulation coordination acc. to EN 50178

Pollution severity	2
--------------------	---

Rated data IEC / EN

Signalling contact	No	Rated voltage (AC)	240 V
Rated current I _N	6.3 A	Voltage type	AC
Fuse protection	6.3 A	Standards	IEC 61984
Acoustic signal	No	Short-circuit current rating I _{SCCR}	25 kA
Integrated back-up fuse	Yes		

Connection data

Stripping length	13 mm	Wire connection method	PUSH IN
Clamping range, rated connection	2.5 mm ²	Wire cross-section, solid, max.	2.5 mm ²
Conductor cross-section, flexible, AEH (DIN 46228-1), max.	2.5 mm ²	Connection cross-section, stranded, min. 0.82 mm ²	
Connection cross-section, stranded, max.	2.5 mm ²		

Electrical data

Voltage type	AC
--------------	----

General data

Protection degree	IP00	Colour	grey
-------------------	------	--------	------

V-ZPA FUSE HOLDER**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Classifications**

ETIM 8.0	EC000941	ETIM 9.0	EC000941
ETIM 10.0	EC000941	ECLASS 14.0	27-17-90-90
ECLASS 15.0	27-17-90-90		