


**SFC-DS 0/12 MC NE WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**SFC – SlimFix Clip MultiCard with two labelling fields**

For conductor markers, it is often required to quickly read the start and destination designation of the respective conductor. Here it makes sense to print both data directly on a marker.

The new SFC-DS markers are designed as MultiCards and are suitable for direct printing with our PrintJet printing system. Their two labelling areas allow multiple data to be printed on a single marker. The print data can be imported directly from CAE projects into the M-Print® PRO marking software. After printing, the markers are placed around the conductor and securely fixed with a special locking mechanism.

**General ordering data**

|            |   |
|------------|---|
| Version    | Conductor and cable markers, 12 x 4.2 mm, white |
| Order No.  | <a href="#">2904970000</a>                      |
| Type       | SFC-DS 0/12 MC NE WS                            |
| GTIN (EAN) | 4099986918481                                   |
| Qty.       | 200 items                                       |

**SFC-DS 0/12 MC NE WS**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Dimensions and weights**

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 3.2 mm | Depth (inches)  | 0.126 inch  |
| Height     | 12 mm  | Height (inches) | 0.4724 inch |
| Width      | 4.2 mm | Width (inches)  | 0.1654 inch |
| Net weight | 0.31 g |                 |             |

**Environmental Product Compliance**

|                          |                             |                  |  |
|--------------------------|-----------------------------|------------------|--|
| RoHS Compliance Status   | Compliant without exemption |                  |  |
| REACH SVHC               | No SVHC above 0.1 wt%       |                  |  |
| Product Carbon Footprint | Cradle to gate              | 0.003 kg CO2 eq. |  |

**General data**

|                                   |              |                                   |                   |
|-----------------------------------|--------------|-----------------------------------|-------------------|
| Type of printing                  | neutral      | Version                           | with snap-in foot |
| Width                             | 4.2 mm       | UL 94 flammability rating         | UL 94, V-2        |
| Operating temperature range, max. | 100 °C       | Operating temperature range, min. | -40 °C            |
| Colour                            | white        | Halogen                           | No                |
| Basic material                    | Polyamide 66 | Printed characters                | without           |
| Size of labelling field           | 11 x 2.2 mm  | Number per roll                   | 40                |

**Conductor and cable markers**

|                                  |                   |                               |                   |
|----------------------------------|-------------------|-------------------------------|-------------------|
| Halogen                          | No                | Conductor cross-section, max. | 1 mm <sup>2</sup> |
| Conductor O.D., max.             | 2.5 mm            | Conductor O.D., min.          | 1.5 mm            |
| Cross-section for connected wire | 1 mm <sup>2</sup> |                               |                   |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |

**Drawings**

