


SFC-DS 1/12 MC NE WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**SFC – SlimFix Clip MultiCard with two labelling fields**

For conductor markers, it is often required to quickly read the start and destination designation of the respective conductor. Here it makes sense to print both data directly on a marker.

The new SFC-DS markers are designed as MultiCards and are suitable for direct printing with our PrintJet printing system. Their two labelling areas allow multiple data to be printed on a single marker. The print data can be imported directly from CAE projects into the M-Print® PRO marking software. After printing, the markers are placed around the conductor and securely fixed with a special locking mechanism.

General ordering data

| | |
|------------|---|
| Version | Conductor and cable markers, 12 x 5.2 mm, white |
| Order No. | 2905030000 |
| Type | SFC-DS 1/12 MC NE WS |
| GTIN (EAN) | 4099986918603 |
| Qty. | 200 items |

SFC-DS 1/12 MC NE WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 4 mm | Depth (inches) | 0.1575 inch |
| Height | 12 mm | Height (inches) | 0.4724 inch |
| Width | 5.2 mm | Width (inches) | 0.2047 inch |
| Net weight | 0.31 g | | |

Environmental Product Compliance

| | | | |
|--------------------------|-----------------------------|------------------|--|
| RoHS Compliance Status | Compliant without exemption | | |
| REACH SVHC | No SVHC above 0.1 wt% | | |
| Product Carbon Footprint | Cradle to gate | 0.003 kg CO2 eq. | |

General data

| | | | |
|-----------------------------------|--------------|-----------------------------------|-------------------|
| Type of printing | neutral | Version | with snap-in foot |
| Width | 5.2 mm | UL 94 flammability rating | UL 94, V-2 |
| Operating temperature range, max. | 100 °C | Operating temperature range, min. | -40 °C |
| Colour | white | Halogen | No |
| Basic material | Polyamide 66 | Printed characters | without |
| Size of labelling field | 11 x 3.2 mm | Number per roll | 40 |

Conductor and cable markers

| | | | |
|----------------------------------|---------------------|-------------------------------|---------------------|
| Halogen | No | Conductor cross-section, max. | 2.5 mm ² |
| Conductor O.D., max. | 3.3 mm | Conductor O.D., min. | 2 mm |
| Cross-section for connected wire | 2.5 mm ² | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |

