


SFC-DS 3/21 MC NE GE**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



SFC – SlimFix Clip MultiCard with two labelling fields
For conductor markers, it is often required to quickly read the start and destination designation of the respective conductor. Here it makes sense to print both data directly on a marker.

The new SFC-DS markers are designed as MultiCards and are suitable for direct printing with our PrintJet printing system. Their two labelling areas allow multiple data to be printed on a single marker. The print data can be imported directly from CAE projects into the M-Print® PRO marking software. After printing, the markers are placed around the conductor and securely fixed with a special locking mechanism.

General ordering data

| | |
|------------|--|
| Version | Conductor and cable markers, 21 x 7 mm, yellow |
| Order No. | 2905190000 |
| Type | SFC-DS 3/21 MC NE GE |
| GTIN (EAN) | 4099986918887 |
| Qty. | 120 items |

SFC-DS 3/21 MC NE GE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 6 mm | Depth (inches) | 0.2362 inch |
| Height | 21 mm | Height (inches) | 0.8268 inch |
| Width | 7 mm | Width (inches) | 0.2756 inch |
| Net weight | 0.68 g | | |

Environmental Product Compliance

| | | | |
|--------------------------|-----------------------------|------------------|--|
| RoHS Compliance Status | Compliant without exemption | | |
| REACH SVHC | No SVHC above 0.1 wt% | | |
| Product Carbon Footprint | Cradle to gate | 0.004 kg CO2 eq. | |

General data

| | | | |
|-----------------------------------|--------------|-----------------------------------|-------------------|
| Type of printing | neutral | Version | with snap-in foot |
| Width | 7 mm | UL 94 flammability rating | V-2, UL 94 |
| Operating temperature range, max. | 100 °C | Operating temperature range, min. | -40 °C |
| Colour | yellow | Halogen | No |
| Basic material | Polyamide 66 | Printed characters | without |
| Size of labelling field | 20 x 5 mm | Number per roll | 24 |

Conductor and cable markers

| | | | |
|----------------------------------|--------------------|-------------------------------|--------------------|
| Halogen | No | Conductor cross-section, max. | 10 mm ² |
| Conductor O.D., max. | 7 mm | Conductor O.D., min. | 4.5 mm |
| Cross-section for connected wire | 10 mm ² | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |

