

VPU AC II+III 4 275/40 S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	Surge voltage arrester, Low voltage, TN-S
Order No.	2907720000
Type	VPU AC II+III 4 275/40 S
GTIN (EAN)	4099986189607
Qty.	1 items

VPU AC II+III 4 275/40 S

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	70 mm	Depth (inches)	2.7559 inch
Height	99 mm	Height (inches)	3.8976 inch
Width	36 mm	Width (inches)	1.4173 inch
Net weight	266 g		

Temperatures

Storage temperature Operating temperature -40 °C...85 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Connection data, remote alert

Connection type Screw connection

General data

Optical function display	green = OK; red = arrester is defective - replace	Segment	Power distribution
Design	Installation housing; 2TE, Insta IP 20	UL 94 flammability rating	V-0
Colour	grey	Protection degree	IP20 in installed state
Mounting rail	TS 35	Operating altitude	≤ 2000 m

Insulation coordination acc. to EN 50178

Surge voltage category III Pollution severity 2

Rated data IEC / EN

Number of poles	4	Combined pulse UOC	6 kV
Signalling contact	No	Rated voltage (AC)	230 V
Low voltage network	TN-S	Voltage type	AC
Temporary surge voltage (over-voltage) - TOV	335 V	Fuse protection	No Fuse necessary ≤100 A gG
Response time / fallback time	≤ 25 ns	Frequency range, max.	60 Hz
Frequency range, min.	50 Hz	Standards	IEC 61643-11, EN 61643-11
Requirements class, acc. to EN 61643-11	T2, T3	Requirements category acc. to IEC 61643-11	Type II, Type III
Max. continuous voltage, U _c (AC)	275 V	Discharge current I _n (8/20μs) wire-PE	20 kA
Discharge current I _{max} (8/20μs) wire-PE	40 kA	Protection level Up at IN (L/N-PE)	≤ 1.5 kV
Short-circuit current rating ISCCR	25 kA	Discharge current (type III)	3 kA
Integrated back-up fuse	No	Protection level Up at IN (L-PE) (type III)	≤1 kV

VPU AC II+III 4 275/40 S

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Connection data

Conductor connection cross-section PE, 35 mm ² stranded, max.		Conductor connection cross-section PE, 35 mm ² solid, max.	
Wire connection method	Screw connection	Type of connection	Screw connection
Stripping length, rated connection	15 mm	Tightening torque, max.	1.2 Nm
Wire cross-section, solid, min.	2.5 mm ²	Wire cross-section, solid, max.	10 mm ²
Wire connection cross section, finely stranded, min.	2.5 mm ²	Wire connection cross section, finely stranded, max.	25 mm ²
Connection cross-section, stranded, min.	2.5 mm ²	Connection cross-section, stranded, max.	10 mm ²

Electrical data

Voltage type	AC
--------------	----

General data

Number of poles	4	Protection degree	IP20 in installed state
Colour	grey		

Guarantee

Time interval	5 years
---------------	---------


Important note

Product information	For use in DC applications, please use the fuse of SIBA Type NH2XL aR/aSF DC 1500 V
---------------------	---

Classifications

ETIM 8.0	EC000941	ETIM 9.0	EC000941
ETIM 10.0	EC000941	ECLASS 14.0	27-17-12-02
ECLASS 15.0	27-17-12-02		

Electric symbol



Schematic circuit diagram

VPU AC II+III 4 275/40 S

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Crosshead screwdriver Phillips



VDE insulated crosshead screwdriver, for Phillips screws, SDIK PH DIN 7438, ISO 8764/2-PH, output to ISO 8764-PH, SoftFinish grip

General ordering data

Type	SDIK PH0 X 60	Version	
Order No.	2749880000	Screwdriver, Blade width (B): 0 mm, 60 mm, Blade thickness (A): 0	
GTIN (EAN)	4050118897081		
Qty.	1 ST		

Spare arrester



General ordering data

Type	VPU AC II+III 0 L-N 275...	Version	
Order No.	2907800000	Surge voltage arrester, Low voltage, Spare arrester, TN-S, TT	
GTIN (EAN)	4099986189676		
Qty.	1 ST		