


VPU AC II+III 3+1 275/20 S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	Surge voltage arrester, Low voltage, TN-C-S, TN-S, TT, IT with N, IT without N
Order No.	2907950000
Type	VPU AC II+III 3+1 275/20 S
GTIN (EAN)	4099986189997
Qty.	1 items

VPU AC II+III 3+1 275/20 S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	70 mm	Depth (inches)	2.7559 inch
Height	97 mm	Height (inches)	3.8189 inch
Width	36 mm	Width (inches)	1.4173 inch
Net weight	263.5 g		

Temperatures

Storage temperature Operating temperature -40 °C...85 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
REACH SVHC No SVHC above 0.1 wt%

General data

Optical function display	green = OK; red = arrester is defective - replace	Segment	Power distribution
Design	Installation housing; 2TE, Insta IP 20	UL 94 flammability rating	V-0
Colour	grey	Protection degree	IP20 in installed state
Mounting rail	TS 35	Operating altitude	≤ 2000 m

Insulation coordination acc. to EN 50178

Surge voltage category III Pollution severity 2

Rated data IEC / EN

Number of poles	4	Combined pulse UOC	6 kV
Signalling contact	No	Rated voltage (AC)	230 V
Low voltage network	TN-C-S, TN-S, TT, IT with N, IT without N	Protection level Up at IN (N-PE)	≤ 1.5 kV
Voltage type	AC	Temporary surge voltage (over-voltage) - 335 V TOV	
Fuse protection	No Fuse necessary ≤100 A gG	Response time / fallback time	≤ 25 ns
Frequency range, max.	60 Hz	Frequency range, min.	50 Hz
Standards	IEC 61643-11, EN 61643-11	Requirements class, acc. to EN 61643-11	T2, T3
Requirements category acc. to IEC 61643-11	Type II, Type III	Max. continuous voltage, U _c (AC)	275 V
Max. continuous voltage, U _c (N-PE)	255 V	Discharge current I _{max} (8/20μs) N-PE	40 kA
Discharge current I _n (8/20μs) N-PE	20 kA	Energy coordination (≤10 m)	Type II, Type III
Discharge current I _n (8/20μs) wire-PE	10 kA	Discharge current I _{max} (8/20μs) wire-PE	20 kA
Protection level Up at IN (L/N-PE)	≤ 1.25 kV	Short-circuit current rating ISCCR	25 kA
Discharge current (type III)	3 kA	Integrated back-up fuse	No
Protection level Up at IN (L-PE) (type III)	≤1 kV	Protection level Up at IN (N-PE) (type III)	≤1 kV

Creation date 15.11.2025 11:22:50 MEZ

Catalogue status / Drawings

VPU AC II+III 3+1 275/20 S

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Connection data

Stripping length	13 mm	Conductor connection cross-section PE, stranded, max.	35 mm ²
Conductor connection cross-section PE, solid, max.	35 mm ²	Wire connection method	Screw connection
Type of connection	Screw connection	Stripping length, rated connection	13 mm
Tightening torque, min.	1.2 Nm	Tightening torque, max.	2 Nm
Clamping range, rated connection	10 mm ²	Clamping range, min.	2.5 mm ²
Clamping range, max.	35 mm ²	Wire cross-section, solid, min.	2.5 mm ²
Wire cross-section, solid, max.	10 mm ²	Wire connection cross section, finely stranded, min.	2.5 mm ²
Wire connection cross section, finely stranded, max.	6 mm ²	Connection cross-section, stranded, min.	2.5 mm ²
Connection cross-section, stranded, max.	10 mm ²		

Electrical data

Voltage type	AC
--------------	----

General data

Number of poles	4	Protection degree	IP20 in installed state
Colour	grey		

Guarantee

Time interval	5 years
---------------	---------


Important note

Product information	For use in DC applications, please use the fuse of SIBA Type NH2XL aR/aSF DC 1500 V
---------------------	---

Classifications

ETIM 7.0	EC000941	ETIM 8.0	EC000941
ETIM 9.0	EC000941	ETIM 10.0	EC000941
ECLASS 12.0	27-17-12-02	ECLASS 13.0	27-17-12-02
ECLASS 14.0	27-17-12-02	ECLASS 15.0	27-17-12-02

Electric symbol



Schematic circuit diagram

VPU AC II+III 3+1 275/20 S

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Crosshead screwdriver Phillips



VDE insulated crosshead screwdriver, for Phillips screws, SDIK PH DIN 7438, ISO 8764/2-PH, output to ISO 8764-PH, SoftFinish grip

General ordering data

Type	SDIK PH0 X 60	Version	
Order No.	2749880000	Screwdriver, Blade width (B): 0 mm, 60 mm, Blade thickness (A): 0	
GTIN (EAN)	4050118897081		
Qty.	1 ST		

Spare arrester



General ordering data

Type	VPU AC II+III 0 L-N 275...	Version	
Order No.	2908010000	Surge voltage arrester, Low voltage, Spare arrester, TN-S, TT	
GTIN (EAN)	4099986190153		
Qty.	1 ST		
Type	VPU AC II+III 0 L/N-PE ...	Version	
Order No.	2908020000	Surge voltage arrester, Low voltage, Spare arrester, TN-S, TT	
GTIN (EAN)	4099986190160		
Qty.	1 ST		