

CA 100 DUO S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

General ordering data

Version	Automatic machines, Automatic stripper and crimper
Order No.	2912430000
Type	CA 100 DUO S
GTIN (EAN)	4099986536005
Qty.	1 items

CA 100 DUO S

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	550 mm	Depth (inches)	21.6535 inch
Height	440 mm	Height (inches)	17.3228 inch
Width	415 mm	Width (inches)	16.3386 inch
Net weight	42000 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cI
REACH SVHC	Lead 7439-92-1

PW65 maintenance - automatic stripping/crimping

Stripping range	4 - 6 mm ² (10 mm ² opt.)/ AWG 12-10 (AWG 8 opt.)	Drive	Electropneumatic
Pulse time	approx. 3 s	Crimping	Trapezoidal
Wire end ferrules cross-section, max.	10 mm ²	Wire end ferrules cross-section, min.	4 mm ²
Crimping range, max.	10 mm ²	Crimping range, min.	4 mm ²
Crimping length	6 - 18 mm	Consumables	with plastic collar
Compressed-air connection	5 - 5.5 bar	Electrical connection	100-240 V / 50/60 Hz / 100 VA

Classifications

ETIM 8.0	EC002778	ETIM 9.0	EC002778
ETIM 10.0	EC002778	ECLASS 14.0	17-13-01-01
ECLASS 15.0	17-13-01-01		