

HDC 06B TSLU 1M20G EXI

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The option of disconnecting cables in the Ex i area simplifies installation and servicing and enables better preparation.

The Rockstar® Ex i enclosures shown here are identified for use by their article designation.

A blue color is therefore not required. A blue Ex i gland is required to complete the enclosure.

General ordering data

Version	HDC enclosures, Installation size: 3, Protection degree: IP65, in plugged condition, Cable entry from side, End-locking clamp, lower side, Standard, Size of cable entries: M 20
Order No.	3001350000
Type	HDC 06B TSLU 1M20G EXI
GTIN (EAN)	4099986902428
Qty.	1 items

HDC 06B TSLU 1M20G EXI

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	74.8 mm	Depth (inches)	2.9449 inch
Height	52 mm	Height (inches)	2.0472 inch
Width	43 mm	Width (inches)	1.6929 inch
Length	74.8 mm	Length (inches)	2.9449 inch
Net weight	124 g		

Temperatures

Limit temperature -40 °C ... 125 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Dimensions

Cable entry	w. thread	Width housing C	43 mm
Total length housing	74.8 mm	Height of housing B	52 mm

General data

Surface finish Powder coating Protection degree IP65, in plugged condition
 Explosion protection type II 2G Ex ib IIC T6 Gb

Version

Number of cable glands	0	Size of cable entries	M 20
Top part/bottom part/lid	upper part	Cover	without cover
Tightening torque	1.2 Nm	Number of cable entry sideways	1
Design of housing	Cable entry from side	Design of locking system	End-locking clamp, lower side
Design	Standard	Installation size	3
Cable entry	w. thread	Type	Plug
Clamp version	End-locking clamp	Sealing	NBR
External thread	M 20	Internal thread	M 20
Colour (RAL)	RAL 7035	BG	3
Suitable for ModuPlug®	No		

Classifications

ETIM 8.0	EC000437	ETIM 9.0	EC000437
ETIM 10.0	EC000437	ECLASS 14.0	27-44-02-02
ECLASS 15.0	27-44-02-02		