


**APGTB 6 FT 2C/1 BK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Some applications demand for a pluggable, modular solution to be more flexible or to facilitate the installation. Where complete functional units have to be prefabricated or replaced, modular and flexible connection systems are required. Our pluggable terminal blocks can be quickly assembled and are completely factory tested.

**General ordering data**

Version	Plug-in modular terminals, PUSH IN, 6 mm <sup>2</sup> , 800 V, 41 A, dark beige
Order No.	<a href="#">3002300000</a>
Type	APGTB 6 FT 2C/1 BK
GTIN (EAN)	4099986903210
Qty.	50 items

## APGTB 6 FT 2C/1 BK

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



UL File Number Search [UL Website](#)  
Certificate No. (cURus) E60693

## Dimensions and weights

Depth	45.5 mm	Depth (inches)	1.7913 inch
Height	66.5 mm	Height (inches)	2.6181 inch
Width	6.1 mm	Width (inches)	0.2402 inch
Net weight	14.13 g		

## Temperatures

Continuous operating temp., min. -60 °C      Continuous operating temp., max. 130 °C

## Environmental Product Compliance

RoHS Compliance Status Compliant without exemption  
REACH SVHC No SVHC above 0.1 wt%

## Material data

Basic material Wemid      Colour dark beige  
Colour of operational elements orange      UL 94 flammability rating V-0

## System specifications

End cover plate required	Yes	Number of potentials	1
Number of levels	1	Number of clamping points per level	1
Levels cross-connected internally	No	PE connection	No
N-function	No	PE function	No
PEN function	No		

## Additional technical data

Open sides	right	Snap-on	No
Type of fixing	Snap-on	Explosion-tested version	No
Type of mounting	TS 35		

## Conductors for clamping (additional connection)

Connection type, additional connection pluggable

## Conductors for clamping (rated connection)

Gauge to IEC 60947-1	A5	Wire connection cross section AWG, max.	AWG 8
Connection direction	top	Stripping length	12 mm
Type of connection	PUSH IN	Number of connections	2
Clamping range, max.	10 mm <sup>2</sup>	Clamping range, min.	0.34 mm <sup>2</sup>

## APGTB 6 FT 2C/1 BK

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

Blade size	1.0 x 5.5 mm	Wire connection cross section AWG, min.	AWG 22
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max.	6 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	0.34 mm <sup>2</sup>
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	6 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	0.34 mm <sup>2</sup>
Wire connection cross section, finely stranded, max.	10 mm <sup>2</sup>	Wire connection cross section, finely stranded, min.	0.34 mm <sup>2</sup>
Connection cross-section, stranded, max.	6 mm <sup>2</sup>	Connection cross-section, stranded, min.	0.34 mm <sup>2</sup>
Wire connection cross-section, solid core, max.	6 mm <sup>2</sup>	Wire connection cross-section, solid core, min.	0.34 mm <sup>2</sup>

### General

Wire connection cross section AWG, max.	AWG 8	Wire connection cross section AWG, min.	AWG 22
---	-------	---	--------

### Rating data

Rated cross-section	6 mm <sup>2</sup>	Rated voltage	800 V
Rated DC voltage	800 V	Nominal current	41 A
Current at maximum wires	41 A	Volume resistance according to IEC 60947-7-x	0.78 mΩ
Rated impulse withstand voltage	8 kV	Power loss in accordance with IEC 60947-7-x	1.31 mW
Surge voltage category	III	Pollution severity	3

### UL rating data

Conductor size Factory wiring max. (cURus)	8 AWG	Voltage size B (cURus)	600 V
Voltage size D (cURus)	600 V	Certificate No. (cURus)	E60693
Conductor size Field wiring min. (cURus)	22 AWG	Conductor size Factory wiring min. (cURus)	22 AWG
Current size B (cURus)	37 A	Voltage size C (cURus)	600 V
Current size C (cURus)	37 A	Current size D (cURus)	5 A
Conductor size Field wiring max. (cURus)	8 AWG		

### Classifications

ETIM 8.0	EC000897	ETIM 9.0	EC000897
ETIM 10.0	EC000897	ECLASS 14.0	27-25-01-17
ECLASS 15.0	27-25-01-17		

**Drawings**



## APGTB 6 FT 2C/1 BK

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

## Accessories

www.weidmueller.com

## Cross-connections



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

## General ordering data

Type	ZQV 6N/10	Version
Order No.	<a href="#">2733970000</a>	Cross-connector (terminal), Plugged, orange, 41 A, Number of poles:
GTIN (EAN)	4064675066811	10, Pitch in mm (P): 8.00, Insulated: Yes, Width: 3.1 mm
Qty.	20 ST	
Type	ZQV 6N/10 BL	Version
Order No.	<a href="#">2786910000</a>	Cross-connector (terminal), Plugged, blue, 41 A, Number of poles: 10,
GTIN (EAN)	4064675064602	Pitch in mm (P): 8.00, Insulated: Yes, Width: 78.7 mm
Qty.	20 ST	
Type	ZQV 6N/2	Version
Order No.	<a href="#">1985740000</a>	Cross-connector (terminal), Plugged, orange, 41 A, Number of poles:
GTIN (EAN)	4050118370362	2, Pitch in mm (P): 8.00, Insulated: Yes, Width: 13.7 mm
Qty.	60 ST	
Type	ZQV 6N/2 BL	Version
Order No.	<a href="#">1985830000</a>	Cross-connector (terminal), Plugged, blue, 41 A, Number of poles: 2,
GTIN (EAN)	4050118370232	Pitch in mm (P): 8.00, Insulated: Yes, Width: 13.7 mm
Qty.	60 ST	
Type	ZQV 6N/3	Version
Order No.	<a href="#">1985760000</a>	Cross-connector (terminal), Plugged, orange, 41 A, Number of poles:
GTIN (EAN)	4050118370263	3, Pitch in mm (P): 8.00, Insulated: Yes, Width: 21.8 mm
Qty.	60 ST	
Type	ZQV 6N/20	Version
Order No.	<a href="#">2810820000</a>	Cross-connector (terminal), Plugged, orange, 41 A, Number of poles:
GTIN (EAN)	4064675283430	20, Pitch in mm (P): 8.00, Insulated: Yes, Width: 4.95 mm
Qty.	20 ST	
Type	ZQV 6N/3 BL	Version
Order No.	<a href="#">1985840000</a>	Cross-connector (terminal), Plugged, blue, 41 A, Number of poles: 3,
GTIN (EAN)	4050118370379	Pitch in mm (P): 8.00, Insulated: Yes, Width: 21.8 mm
Qty.	60 ST	
Type	ZQV 6N/4	Version
Order No.	<a href="#">1985780000</a>	Cross-connector (terminal), Plugged, orange, 41 A, Number of poles:
GTIN (EAN)	4050118370287	4, Pitch in mm (P): 8.00, Insulated: Yes, Width: 29.9 mm
Qty.	60 ST	
Type	ZQV 6N/4 BL	Version
Order No.	<a href="#">1985850000</a>	Cross-connector (terminal), Plugged, blue, 41 A, Number of poles: 4,
GTIN (EAN)	4050118370447	Pitch in mm (P): 8.00, Insulated: Yes, Width: 29.9 mm
Qty.	60 ST	
Type	ZQV 6N/6	Version
Order No.	<a href="#">2733950000</a>	Cross-connector (terminal), Plugged, orange, 41 A, Number of poles:
GTIN (EAN)	4064675066699	6, Pitch in mm (P): 8.00, Insulated: Yes, Width: 3.1 mm
Qty.	20 ST	

## APGTB 6 FT 2C/1 BK

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

Type	ZQV 6N/6 BL	Version
Order No.	<a href="#">2786890000</a>	Cross-connector (terminal), Plugged, blue, 41 A, Number of poles: 6,
GTIN (EAN)	4064675064572	Pitch in mm (P): 8.00, Insulated: Yes, Width: 46.3 mm
Qty.	20 ST	
Type	ZQV 6N/7	Version
Order No.	<a href="#">2733960000</a>	Cross-connector (terminal), Plugged, orange, 41 A, Number of poles:
GTIN (EAN)	4064675066804	7, Pitch in mm (P): 8.00, Insulated: Yes, Width: 3.1 mm
Qty.	20 ST	
Type	ZQV 6N/7 BL	Version
Order No.	<a href="#">2786900000</a>	Cross-connector (terminal), Plugged, blue, 41 A, Number of poles: 7,
GTIN (EAN)	4064675064596	Pitch in mm (P): 8.00, Insulated: Yes, Width: 54.4 mm
Qty.	20 ST	

## End bracket



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

## General ordering data

Type	AEB 35 SC/1	Version
Order No.	<a href="#">1991920000</a>	A-series, End bracket
GTIN (EAN)	4050118376722	
Qty.	50 ST	
Type	AEB 35 SC/1 BK	Version
Order No.	<a href="#">2475310000</a>	A-series, End bracket
GTIN (EAN)	4050118487114	
Qty.	50 ST	
Type	AEB 35 SC/1 RM	Version
Order No.	<a href="#">3112300000</a>	A-series, End bracket
GTIN (EAN)	4099987196413	
Qty.	50 ST	
Type	AEB 35 SCL/1 RM	Version
Order No.	<a href="#">3112310000</a>	A-series, End bracket
GTIN (EAN)	4099987196420	
Qty.	20 ST	
Type	AEB 35 SCL/1 V0	Version
Order No.	<a href="#">2661280000</a>	A-series, End bracket
GTIN (EAN)	4050118702163	
Qty.	20 ST	
Type	AEB 35 SCL/1 V0 BK	Version
Order No.	<a href="#">2661300000</a>	A-series, End bracket
GTIN (EAN)	4050118702187	
Qty.	20 ST	

## APGTB 6 FT 2C/1 BK

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Accessories

Type	AEB 35 SCL/1 V0 GY	Version
Order No.	<a href="#">2661290000</a>	A-series, End bracket
GTIN (EAN)	4050118702170	
Qty.	20 ST	

### End plates and partition plates



Partition plates and end plates are essential accessories for terminal blocks. Partition plates provide optical and electrical separation of different potentials and functional groups, increasing safety and ensuring a clear structure inside the control cabinet. End plates close the terminal block row on the sides, protect against contact with live parts, and ensure a clean, stable finish. Both components are precisely matched to the respective Weidmüller terminal block series, contributing to safe, compliant, and professional wiring.

#### General ordering data

Type	AEP 2C 6	Version
Order No.	<a href="#">1991970000</a>	A-series, End plate
GTIN (EAN)	4050118376692	
Qty.	50 ST	
Type	AEP 2C 6 BL	Version
Order No.	<a href="#">1991950000</a>	A-series, End plate
GTIN (EAN)	4050118376739	
Qty.	50 ST	
Type	AEP 2C 6 OR	Version
Order No.	<a href="#">2052520000</a>	A-series, End plate
GTIN (EAN)	4050118412123	
Qty.	50 ST	

### Plugs



The plugs for our WeiCoS-System are available for all different connection systems. The product range includes preassembled connectors from 1 to 10 poles and the possibility of an individual assembly. This ensures maximum flexibility for every application. The customized accessories increase the safety and protection against environmental influences.

#### General ordering data

Type	APGCE	Version
Order No.	<a href="#">1514490000</a>	Coding element (terminal), Wemid, orange, Width: 3.3 mm
GTIN (EAN)	4050118321906	
Qty.	50 ST	
Type	APG 6 L BK	Version
Order No.	<a href="#">3002500000</a>	Plug, 6 mm <sup>2</sup> , 800 V, 41 A, Number of poles: 1, dark beige
GTIN (EAN)	4099986903371	
Qty.	50 ST	

## APGTB 6 FT 2C/1 BK

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

Type	APG 6 L BL	Version
Order No.	<a href="#">3002490000</a>	Plug, 6 mm <sup>2</sup> , 800 V, 41 A, Number of poles: 1, dark beige
GTIN (EAN)	4099986903364	
Qty.	50 ST	
Type	APG 6 L GN	Version
Order No.	<a href="#">3002480000</a>	Plug, 6 mm <sup>2</sup> , 800 V, 41 A, Number of poles: 1, dark beige
GTIN (EAN)	4099986903357	
Qty.	50 ST	
Type	APG 6 L OR	Version
Order No.	<a href="#">3002520000</a>	Plug, 6 mm <sup>2</sup> , 800 V, 41 A, Number of poles: 1, dark beige
GTIN (EAN)	4099986903395	
Qty.	50 ST	
Type	APG 6 L RD	Version
Order No.	<a href="#">3002510000</a>	Plug, 6 mm <sup>2</sup> , 800 V, 41 A, Number of poles: 1, dark beige
GTIN (EAN)	4099986903388	
Qty.	50 ST	
Type	APG 6 MI BK	Version
Order No.	<a href="#">3002450000</a>	Plug, 6 mm <sup>2</sup> , 800 V, 41 A, Number of poles: 1, dark beige
GTIN (EAN)	4099986903326	
Qty.	50 ST	
Type	APG 6 MI BL	Version
Order No.	<a href="#">3002440000</a>	Plug, 6 mm <sup>2</sup> , 800 V, 41 A, Number of poles: 1, dark beige
GTIN (EAN)	4099986903319	
Qty.	50 ST	
Type	APG 6 MI GN	Version
Order No.	<a href="#">3002430000</a>	Plug, 6 mm <sup>2</sup> , 800 V, 41 A, Number of poles: 1, dark beige
GTIN (EAN)	4099986903302	
Qty.	50 ST	
Type	APG 6 MI OR	Version
Order No.	<a href="#">3002470000</a>	Plug, 6 mm <sup>2</sup> , 800 V, 41 A, Number of poles: 1, dark beige
GTIN (EAN)	4099986903340	
Qty.	50 ST	
Type	APG 6 MI RD	Version
Order No.	<a href="#">3002460000</a>	Plug, 6 mm <sup>2</sup> , 800 V, 41 A, Number of poles: 1, dark beige
GTIN (EAN)	4099986903333	
Qty.	50 ST	
Type	APG 6 R BK	Version
Order No.	<a href="#">3002380000</a>	Plug, 6 mm <sup>2</sup> , 800 V, 41 A, Number of poles: 1, dark beige
GTIN (EAN)	4099986903272	
Qty.	50 ST	
Type	APG 6 R BL	Version
Order No.	<a href="#">3002370000</a>	Plug, 6 mm <sup>2</sup> , 800 V, 41 A, Number of poles: 1, dark beige
GTIN (EAN)	4099986903265	
Qty.	50 ST	
Type	APG 6 R GN	Version
Order No.	<a href="#">3002350000</a>	Plug, 6 mm <sup>2</sup> , 800 V, 41 A, Number of poles: 1, dark beige
GTIN (EAN)	4099986903258	
Qty.	50 ST	
Type	APG 6 R OR	Version
Order No.	<a href="#">3002400000</a>	Plug, 6 mm <sup>2</sup> , 800 V, 41 A, Number of poles: 1, dark beige
GTIN (EAN)	4099986903296	
Qty.	50 ST	

## APGTB 6 FT 2C/1 BK

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

### Accessories

Type	APG 6 R RD	Version
Order No.	<a href="#">3002390000</a>	Plug, 6 mm <sup>2</sup> , 800 V, 41 A, Number of poles: 1, dark beige
GTIN (EAN)	4099986903289	
Qty.	50 ST	
Type	APG 6/10	Version
Order No.	<a href="#">2829070000</a>	Plug, 6 mm <sup>2</sup> , 800 V, 41 A, Number of poles: 10, beige
GTIN (EAN)	4064675382782	
Qty.	10 ST	
Type	APG 6/2	Version
Order No.	<a href="#">2882750000</a>	Plug, 6 mm <sup>2</sup> , 800 V, 41 A, Number of poles: 2, beige
GTIN (EAN)	4064675758273	
Qty.	25 ST	
Type	APG 6/3	Version
Order No.	<a href="#">2882690000</a>	Plug, 6 mm <sup>2</sup> , 800 V, 41 A, Number of poles: 3, beige
GTIN (EAN)	4064675758211	
Qty.	25 ST	
Type	APG 6/4	Version
Order No.	<a href="#">2829060000</a>	Plug, 6 mm <sup>2</sup> , 800 V, 41 A, Number of poles: 4, beige
GTIN (EAN)	4064675382768	
Qty.	25 ST	
Type	APG 6/5	Version
Order No.	<a href="#">2882700000</a>	Plug, 6 mm <sup>2</sup> , 800 V, 41 A, Number of poles: 5, beige
GTIN (EAN)	4064675758228	
Qty.	25 ST	
Type	APG 6/6	Version
Order No.	<a href="#">2882710000</a>	Plug, 6 mm <sup>2</sup> , 800 V, 41 A, Number of poles: 6, beige
GTIN (EAN)	4064675758235	
Qty.	25 ST	
Type	APG 6/7	Version
Order No.	<a href="#">2882720000</a>	Plug, 6 mm <sup>2</sup> , 800 V, 41 A, Number of poles: 7, beige
GTIN (EAN)	4064675758242	
Qty.	20 ST	
Type	APG 6/8	Version
Order No.	<a href="#">2882730000</a>	Plug, 6 mm <sup>2</sup> , 800 V, 41 A, Number of poles: 8, beige
GTIN (EAN)	4064675758259	
Qty.	20 ST	
Type	APG 6/9	Version
Order No.	<a href="#">2882740000</a>	Plug, 6 mm <sup>2</sup> , 800 V, 41 A, Number of poles: 9, beige
GTIN (EAN)	4064675758266	
Qty.	10 ST	

## APGTB 6 FT 2C/1 BK

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
  - Strips for fast installation
  - Terminal markers, suitable for all Weidmüller cable connectors
  - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

#### General ordering data

Type	DEK 5/8 MC NE WS	Version	
Order No.	<a href="#">1856740000</a>		Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00
GTIN (EAN)	4032248400850		Weidmueller, white
Qty.	800 ST		

### Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
  - Strips for fast installation
  - Terminal markers, suitable for all Weidmüller cable connectors
  - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

#### General ordering data

Type	DEK 5/8 MC SDR	Version	
Order No.	<a href="#">1856750000</a>		Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00
GTIN (EAN)	4032248400867		Weidmueller, To customer specification
Qty.	160 ST		
Type	DEK 5/8 PLUS MC SDR	Version	
Order No.	<a href="#">1046370000</a>		Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00
GTIN (EAN)	4032248782079		Weidmueller, To customer specification
Qty.	160 ST		

## APGTB 6 FT 2C/1 BK

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Accessories

### Plus



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
  - Strips for fast installation
  - Terminal markers, suitable for all Weidmüller cable connectors
  - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

Type	DEK 5/8 PLUS MC NE WS	Version	
Order No.	<a href="#">1046350000</a>		Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00
GTIN (EAN)	4032248782055		Weidmueller, white
Qty.	800 ST		

### DEK 5/8



#### WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

### General ordering data

Type	DEK 5/8 MM WS	Version	
Order No.	<a href="#">2007130000</a>		Dekafix, Terminal marker, 5 x 8 mm, Weidmueller, white
GTIN (EAN)	4050118392012		
Qty.	500 ST		

## APGTB 6 FT 2C/1 BK

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

## Accessories

www.weidmueller.com

### WS 8/8



#### WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.


Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

#### General ordering data

Type	WS-A 8/8 MM WS	Version	
Order No.	<a href="#">2448930000</a>	WS, Terminal marker, 8 x 8.1 mm, Weidmueller, white	
GTIN (EAN)	4050118462982		
Qty.	500 ST		

### Plugs



The plugs for our WeiCoS-System are available for all different connection systems. The product range includes preassembled connectors from 1 to 10 poles and the possibility of an individual assembly. This ensures maximum flexibility for every application. The customized accessories increase the safety and protection against environmental influences.

#### General ordering data

Type	APG 6/1	Version	
Order No.	<a href="#">2762320000</a>	Plug, 6 mm <sup>2</sup> , 500 V, 30 A, Number of poles: 1, dark beige	
GTIN (EAN)	4064675021322		
Qty.	50 ST		

## APGTB 6 FT 2C/1 BK

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Testadapter and testsockets



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

### General ordering data

Type	FZS 2/4 RT/80 SAKT4	Version	
Order No.	<a href="#">1276300000</a>	Plug (terminal), Plug-in connection, 2 mm <sup>2</sup> , Number of connections: 2,	
GTIN (EAN)	4008190026080	Number of poles: 1, Width: 9 mm	
Qty.	20 ST		