



CH-SMR-00.33-ECS180 VPE10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Base counter, gateway, control box and overvoltage protection device are connected with pre-assembled cable sets as point-to-point or Y-assembly. Weidmüller offers the right connection solutions for this, conforming to FNN and DIN-VDE 0603 standards. Pre-assembled power cables with 6kV overvoltage protection round up the portfolio.

General ordering data

Version	Smart Metering Cable Assemblies, 6 kV, IP30, in plugged and mounted condition, 300 V, Li9YH 1 x 0,75, 0.33 m
Order No.	2924850033
Type	CH-SMR-00.33-ECS180 VPE10
GTIN (EAN)	4099986795723
Qty.	10 items

CH-SMR-00.33-ECS180 VPE10

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Net weight 11.77 g

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

General Technical Data

Number of poles	2	Applications	Indoor
Rated impulse withstand voltage	6 kV	Nominal voltage	300 V
Nominal current	9 A	Standards	DIN VDE 0603-100
Protection degree	IP30, in plugged and mounted condition	Surge voltage category	III
Pollution severity	3		

Technical Specifications Connector

Connector	Connector description	Connector 1
	Cable entry	straight
	Housing main material	PA
	Number of poles	2
	Type	Male
	Connector description	Connector 6
Connector	Cable entry	straight
	Number of poles	2

Technical specifications for cable

Cable length	0.33 m	Line type	Li9YH 1 x 0,75
Sheathing colour	black / blue	Resistance to oils	No
Core cross-section	0.75 mm ²	Number of wires	2
Shielded	No	Halogen	No
Insulation	PP	Temperature range, moving, max.	90 °C
Temperature range, moving, min.	-25 °C	Temperature range, stationary, max.	90 °C
Temperature range, stationary, min.	-30 °C	Cable Material	Polyolefine
Bending radius, min., moving	15 x cable diameter	Bending radius, min., stationary	8 x cable diameter
Outside diameter	2.35 mm ± 0.15 mm		

Important note

IPC conformity Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.


Notes unenclosed connector, without breaking capacity (COC), acc. DIN EN 61984 (VDE 0627)

Technical data

Classifications

ETIM 8.0	EC001576	ETIM 9.0	EC001576
ETIM 10.0	EC001576	ECLASS 14.0	27-06-04-02
ECLASS 15.0	27-06-04-02		

Dimensional drawing



Dimensional drawing

Steckverbinder Bauform 6
Connector type 6
24 H8.75/180

