

**IE-C6EB8BV0100XCAXCA-X**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Assembled IE cables, railway cable, Cat.7, violet, M12

**General ordering data**

Version	System cable, M12 X-type IP67 male, angled, M12 X-type IP67 male, angled, Cat. 6, Polyolefine, molecularly interlinked, 10 m
Order No.	<a href="#">2927570100</a>
Type	IE-C6EB8BV0100XCAXCA-X
GTIN (EAN)	4099987855815
Qty.	1 items

## IE-C6EB8BV0100XCAXCA-X

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Length	10 m	Length (inches)	393.7008 inch
Net weight	280 g		

## Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	
---------------------	----------------	-----------------------	--

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1

## Cable specific standards

Fluorine content	According to EN-50267-2-1	Flames propagate vertically on bundled cables	EN 60332-3-25
Corrosiveness of fumes	EN 50267-2-2	Fire safety for railway vehicles	According to EN 45545, HL1 - HL3, According to NFPA 130
Impervious to smoke	According to IEC 61034-2	Poisonous gases	EN 50305

## Electrical properties

Insulation resistance	≥ 100 MΩ
-----------------------	----------

## General standards

Connector standard	IEC 61076-2-109
--------------------	-----------------

## Cable structure

Strands	7	Sheathing colour	violet
Cross-section	4*2*AWG 26/7 - 4*2*0.128 mm <sup>2</sup>	Shielding	S/FTP
Number of wires	8	Insulation cross-section	1.05 mm
Sheath diameter, max.	6.8 mm	Sheath diameter, min.	6.4 mm
Material sheath	Polyolefine, molecularly interlinked	Wire pair shielding	Plastic foil
Colour coding	white / orange, orange, white / green, green, white / brown, brown, white / blue, blue		

## Electrical properties of cable

Rated voltage (AC)	50 V	Rated voltage (DC)	60 V
Insulation resistance	≥ 100 MΩ	Category	Cat. 6

## Mechanical and material properties of cable

Resistance to oils	in accordance with IEC 60811:404	Halogen	No
Min. bending radius, once only	6 *diameter	Abrasion resistance	very good

## IE-C6EB8BV0100XCAXCA-X

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

Resistance to spread of flame	in accordance with IEC 60332-1-2	Corrosiveness of fumes	EN 50267-2-2
Impervious to smoke	According to IEC 61034-2		

### Plug, left

Plug left	M12, X-coded, IP67, male contact, angled 0°, plug, Plastic, shielded
-----------	--

### Plug, right

Plug right	M12, X-coded, IP67, male contact, angled 0°, plug, Plastic, shielded
------------	--

### Classifications

ETIM 8.0	EC002599	ETIM 9.0	EC002599
ETIM 10.0	EC002599	ECLASS 14.0	27-06-03-08
ECLASS 15.0	27-06-03-08		

Drawings

Wiring

M12	1	White, Orange	1	M12
	2	Orange	2	
	3	White, Green	3	
	4	Green	4	
	5	White, Brown	5	
	6	Brown	6	
	7	White, Blue	7	
	8	Blue	8	

Pinning

