

TC INL THIRD 11**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Inspired by 5S and lean management methods, Weidmüller foam inserts ensure an efficient and tidy workplace. Designed according to a modular principle, they offer many advantages and can be selected according to individual requirements.

General ordering data

Order No.	2929310000
Type	TC INL THIRD 11
GTIN (EAN)	4099986664098
Qty.	1 items

TC INL THIRD 11

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	50 mm	Depth (inches)	1.9685 inch
Height	446 mm	Height (inches)	17.559 inch
Width	200 mm	Width (inches)	7.874 inch
Net weight	817.09 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	1eacbb3e-7931-4ebb-9179-f29fd9b50028

Technical data

Description of article	Foam inlay wrenches
------------------------	---------------------

Classifications

ETIM 6.0	EC011819	ETIM 7.0	EC011819
ETIM 8.0	EC011819	ETIM 9.0	EC011819
ETIM 10.0	EC011819	ECLASS 9.1	21-07-92-03
ECLASS 10.0	21-07-92-03	ECLASS 11.0	21-07-04-12
ECLASS 12.0	21-07-04-12	ECLASS 13.0	21-07-04-12
ECLASS 14.0	21-07-04-12	ECLASS 15.0	21-07-04-12

TC INL THIRD 11

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Hexagon socket



Hexagon screwdriver with cross-grip made from high-quality plastics

- Surface nickel-plated
- Made from hardened chromium-vanadium steel
- According to DIN 6911
- Designed for screws acc. to DIN 6912

General ordering data

Type	SDQ T HANDLE HEX 4	Version
Order No.	2888290000	Mounting tool, Blade length: 150 mm
GTIN (EAN)	4064675875338	
Qty.	1 ST	
Type	SDQ T HANDLE HEX 5	Version
Order No.	2888300000	Mounting tool, Blade length: 200 mm
GTIN (EAN)	4064675875345	
Qty.	1 ST	
Type	SDQ T HANDLE HEX 6	Version
Order No.	2888310000	Mounting tool, Blade length: 200 mm
GTIN (EAN)	4064675875352	
Qty.	1 ST	

Bit holder



If you demand effective and exact work, it is essential to use the precise torque. This also guarantees high repetition accuracy.

This is the perfect job for the new Weidmüller torque screwdriver with the ergonomic grip and the unique interchangeable bit system.

- Compact and especially light design
- Torque set with special tool (supplied); an unintended, incorrect setting is ruled out.
- Ergonomic handle sizes matched to the torque range.
- Tools subjected to routine testing and provided with an ID number; 100% quality control with verification and product reference.
- Clicking sound upon reaching the set torque, clearly audible and noticeable, no unnecessary tightening.
- Interchangeable blades made from high-quality wear-resistant tool steel.
- All tools fulfil the accuracy requirements of: EN ISO 6798, BS EN 26789, ASME B107.14M
- Trigger accuracy +/- 6% of the set scale value.

General ordering data

Type	SDQ T HANDLE BITHOLDER ...	Version
Order No.	2888370000	Mounting tool, Blade length: 129 mm
GTIN (EAN)	4064675875413	
Qty.	1 ST	

TC INL THIRD 11

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Type	SD BITHOLDER 1/4	Version
Order No.	2888380000	Mounting tool
GTIN (EAN)	4064675875420	
Qty.	1 ST	

Bits 25 mm for bitholder

General ordering data

Type	BIT C 6,3 0,5X3,0X25	Version
Order No.	2748860000	Mounting tool, Blade width (B): 3 mm, Blade length: 25 mm, Blade thickness (A): 0.5 mm
GTIN (EAN)	4050118894738	
Qty.	5 ST	
Type	BIT C 6,3 0,5X3,5X25	Version
Order No.	2748870000	Mounting tool, Blade width (B): 3.5 mm, Blade length: 25 mm, Blade thickness (A): 0.5 mm
GTIN (EAN)	4050118894745	
Qty.	5 ST	
Type	BIT C 6,3 0,5X4,0X25	Version
Order No.	2748880000	Mounting tool, Blade width (B): 4 mm, Blade length: 25 mm, Blade thickness (A): 0.5 mm
GTIN (EAN)	4050118894752	
Qty.	5 ST	
Type	BIT C 6,3 0,8X5,5X25	Version
Order No.	2748890000	Mounting tool, Blade width (B): 5.5 mm, Blade length: 25 mm, Blade thickness (A): 0.8 mm
GTIN (EAN)	4050118894769	
Qty.	5 ST	
Type	BIT C 6,3 PH0X25	Version
Order No.	2748140000	Mounting tool, Blade length: 25 mm, Blade size, crosshead: 0
GTIN (EAN)	4050118894677	
Qty.	5 ST	
Type	BIT C 6,3 PH1X25	Version
Order No.	2748150000	Mounting tool, Blade width (B): 1 mm, Blade length: 25 mm, Blade thickness (A): 1 mm, Blade size, crosshead: 1
GTIN (EAN)	4050118894684	
Qty.	5 ST	
Type	BIT C 6,3 PH2X25	Version
Order No.	2748160000	Mounting tool, Blade width (B): 2 mm, Blade length: 25 mm, Blade thickness (A): 2 mm, Blade size, crosshead: 2
GTIN (EAN)	4050118894691	
Qty.	5 ST	
Type	BIT C 6,3 PZ0X25	Version
Order No.	2748170000	Mounting tool, Blade length: 25 mm, Blade size, crosshead: 0
GTIN (EAN)	4050118894707	
Qty.	5 ST	

TC INL THIRD 11

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	BIT C 6,3 PZ1X25	Version
Order No.	2748180000	Mounting tool, Blade width (B): 1 mm, Blade length: 25 mm, Blade
GTIN (EAN)	4050118894714	thickness (A): 1 mm, Blade size, crosshead: 1
Qty.	5 ST	
Type	BIT C 6,3 PZ2X25	Version
Order No.	2748190000	Mounting tool, Blade width (B): 2 mm, Blade length: 25 mm, Blade
GTIN (EAN)	4050118894721	thickness (A): 2 mm, Blade size, crosshead: 2
Qty.	5 ST	

E6.3 bit holder



The Weidmüller bits are standard bits which are highly popular with users thanks to their good quality, large range and efficiency. The computer-controlled hardening method enables Weidmüller to guarantee a consistently high standard of quality.

The high-quality raw materials used make it possible to reach torques far higher than any of those specified in the relevant DIN standards:

- DIN 5261 for PH/PZ bits,
- DIN 5263 for slotted bits,
- Camcar standard for TORX bits

That means a long life at high torques and hence ideal conditions for standard situations.

The benefits:

- Suitable for all types of screws. Because of their excellent hardness values of 59-61 HRC, they are suitable for use with both manual and power tools.
- Good wearing resistance and thus a long life expectancy.
- Optimum fit in all DIN screws means low wear and optimum torque transmission.
- Manufactured to meet professional quality criteria according to relevant ISO standards with a consistently high standard of quality.

General ordering data

Type	UBH 1/4 E6,3	Version
Order No.	2748200000	Mounting tool
GTIN (EAN)	4050118895339	
Qty.	5 ST	

Hexagon socket



Hexagon screwdriver with cross-grip made from high-quality plastics

- Surface nickel-plated
- Made from hardened chromium-vanadium steel
- According to DIN 6911
- Designed for screws acc. to DIN 6912

TC INL THIRD 11

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

General ordering data

Type	SDQ T HANDLE HEX 4	Version
Order No.	2888290000	Mounting tool, Blade length: 150 mm
GTIN (EAN)	4064675875338	
Qty.	1 ST	
Type	SDQ T HANDLE HEX 5	Version
Order No.	2888300000	Mounting tool, Blade length: 200 mm
GTIN (EAN)	4064675875345	
Qty.	1 ST	
Type	SDQ T HANDLE HEX 6	Version
Order No.	2888310000	Mounting tool, Blade length: 200 mm
GTIN (EAN)	4064675875352	
Qty.	1 ST	

Bit holder



- If you demand effective and exact work, it is essential to use the precise torque. This also guarantees high repetition accuracy.
- This is the perfect job for the new Weidmüller torque screwdriver with the ergonomic grip and the unique interchangeable bit system.
- Compact and especially light design
 - Torque set with special tool (supplied); an unintended, incorrect setting is ruled out.
 - Ergonomic handle sizes matched to the torque range.
 - Tools subjected to routine testing and provided with an ID number; 100% quality control with verification and product reference.
 - Clicking sound upon reaching the set torque, clearly audible and noticeable, no unnecessary tightening.
 - Interchangeable blades made from high-quality wear-resistant tool steel.
 - All tools fulfil the accuracy requirements of: EN ISO 6798, BS EN 26789, ASME B107.14M
 - Trigger accuracy +/- 6% of the set scale value.

General ordering data

Type	SDQ T HANDLE BITHOLDER ...	Version
Order No.	2888370000	Mounting tool, Blade length: 129 mm
GTIN (EAN)	4064675875413	
Qty.	1 ST	
Type	SD BITHOLDER 1/4	Version
Order No.	2888380000	Mounting tool
GTIN (EAN)	4064675875420	
Qty.	1 ST	

Accessories

Bits 25 mm for bitholder

General ordering data

Type	BIT C 6,3 0,5X3,0X25	Version
Order No.	2748860000	Mounting tool, Blade width (B): 3 mm, Blade length: 25 mm, Blade
GTIN (EAN)	4050118894738	thickness (A): 0.5 mm
Qty.	5 ST	
Type	BIT C 6,3 0,5X3,5X25	Version
Order No.	2748870000	Mounting tool, Blade width (B): 3.5 mm, Blade length: 25 mm, Blade
GTIN (EAN)	4050118894745	thickness (A): 0.5 mm
Qty.	5 ST	
Type	BIT C 6,3 0,5X4,0X25	Version
Order No.	2748880000	Mounting tool, Blade width (B): 4 mm, Blade length: 25 mm, Blade
GTIN (EAN)	4050118894752	thickness (A): 0.5 mm
Qty.	5 ST	
Type	BIT C 6,3 0,8X5,5X25	Version
Order No.	2748890000	Mounting tool, Blade width (B): 5.5 mm, Blade length: 25 mm, Blade
GTIN (EAN)	4050118894769	thickness (A): 0.8 mm
Qty.	5 ST	
Type	BIT C 6,3 PH0X25	Version
Order No.	2748140000	Mounting tool, Blade length: 25 mm, Blade size, crosshead: 0
GTIN (EAN)	4050118894677	
Qty.	5 ST	
Type	BIT C 6,3 PH1X25	Version
Order No.	2748150000	Mounting tool, Blade width (B): 1 mm, Blade length: 25 mm, Blade
GTIN (EAN)	4050118894684	thickness (A): 1 mm, Blade size, crosshead: 1
Qty.	5 ST	
Type	BIT C 6,3 PH2X25	Version
Order No.	2748160000	Mounting tool, Blade width (B): 2 mm, Blade length: 25 mm, Blade
GTIN (EAN)	4050118894691	thickness (A): 2 mm, Blade size, crosshead: 2
Qty.	5 ST	
Type	BIT C 6,3 PZ0X25	Version
Order No.	2748170000	Mounting tool, Blade length: 25 mm, Blade size, crosshead: 0
GTIN (EAN)	4050118894707	
Qty.	5 ST	
Type	BIT C 6,3 PZ1X25	Version
Order No.	2748180000	Mounting tool, Blade width (B): 1 mm, Blade length: 25 mm, Blade
GTIN (EAN)	4050118894714	thickness (A): 1 mm, Blade size, crosshead: 1
Qty.	5 ST	
Type	BIT C 6,3 PZ2X25	Version
Order No.	2748190000	Mounting tool, Blade width (B): 2 mm, Blade length: 25 mm, Blade
GTIN (EAN)	4050118894721	thickness (A): 2 mm, Blade size, crosshead: 2
Qty.	5 ST	

Accessories**E6.3 bit holder**

The Weidmüller bits are standard bits which are highly popular with users thanks to their good quality, large range and efficiency. The computer-controlled hardening method enables Weidmüller to guarantee a consistently high standard of quality.

The high-quality raw materials used make it possible to reach torques far higher than any of those specified in the relevant DIN standards:

- DIN 5261 for PH/PZ bits,
- DIN 5263 for slotted bits,
- Camcar standard for TORX bits

That means a long life at high torques and hence ideal conditions for standard situations.

The benefits:

- Suitable for all types of screws. Because of their excellent hardness values of 59-61 HRC, they are suitable for use with both manual and power tools.
- Good wearing resistance and thus a long life expectancy.
- Optimum fit in all DIN screws means low wear and optimum torque transmission.
- Manufactured to meet professional quality criteria according to relevant ISO standards with a consistently high standard of quality.

General ordering data

Type	UBH 1/4 E6,3	Version
Order No.	2748200000	Mounting tool
GTIN (EAN)	4050118895339	
Qty.	5 ST	