

UV66-ADV-15-CAP-W-V2**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germanywww.weidmueller.com

u-view Advanced touch panels from Weidmüller offer excellent image quality and can be used in most industrial environments. The portfolio features various screen sizes from 7" to 21.5" and has high-resolution capacitive touchscreens with support for swipe gestures and glove operation. All panels are equipped with a Linux operating system and an HTML5-capable browser and are optimised for web applications through the integrated kiosk mode and their simple configuration. As a result, they are the perfect solution for web-based visualisations and enable access to a variety of web servers, such as u-OS, u-create PROCON-WEB, u-control web and many more. The panels have a particularly flat design, with an industrial IP66 housing.

General ordering data

Order No.	2932860000
Type	UV66-ADV-15-CAP-W-V2
GTIN (EAN)	4099986674189
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Last order date	2026-06-26T00:00:00+02:00
Alternative product	UV66-ADV-15-CAP-W-V2

UV66-ADV-15-CAP-W-V2

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E230683

Dimensions and weights

Depth	52 mm	Depth (inches)	2.0472 inch
Height	269 mm	Height (inches)	10.5905 inch
Width	419.7 mm	Width (inches)	16.5236 inch
Wall thickness, min.	1 mm	Wall thickness, max.	6 mm
Net weight	3780 g		

Temperatures

Storage temperature	-30 °C ... +70 °C	Operating temperature	-20 °C ... 60 °C
Humidity	95% relative humidity, non-condensing @ 40°C		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cl
REACH SVHC	Lead 7439-92-1, 1, 2-dimethoxyethane; ethylene glycol dimethyl ether (EGDME) 110-71-4
SCIP	84ae9d99-1662-4798-ad33-3fe26637f337

Equipment

Size	15.6"	Resolution	1920 x 1080
Number of displayable colours	16200000	Luminance	450 cd/m²
Touch-Screen	Projected capacitive (P-CAP)	Material display	Tempered glass
Material frame	Aluminium		

General data

Protection degree	Built-in: IP66, Enclosure: IP20	
Operating system	Linux Yocto 4.2	
Voltage supply range	Voltage type	DC
	Voltage, min.	19.2 V
	Voltage, max.	28.8 V
Voltage supply	24 V DC	
Power consumption	Power consumption, nominal	21.4 W
	Power consumption, max.	28.8 W
MTBF with LCD	5.23 a	

System data

Memory (RAM)	4 GB	Interface	2x USB 2.0, 2 x Ethernet 10/100/1000 MBit/s (RJ45)
Operating system	Linux Yocto 4.2	Memory	16 MB

UV66-ADV-15-CAP-W-V2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data**

Interfaces behind	2x USB 2.0, 2 x Ethernet 10/100/1000 MBit/s (RJ45)	Processor	NXP® ARM® Cortex™- A53 i.MX 8M Mini
Memory (Flash)	16 GB		

Classifications

ETIM 8.0	EC001412	ETIM 9.0	EC001412
ETIM 10.0	EC001412	ECLASS 14.0	27-33-02-01
ECLASS 15.0	27-33-02-01		


UV66-ADV-15-CAP-W-V2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com


Drawings

Maße (mm) / Dimensions (mm)



	LCD	A	B	C	D	E
UV66-ADV-7-CAP-W-V2	7"	205	146,9	25	52	7
UV66-ADV-10-CAP-W-V2	10.1"	283,1	202,3	25	52	7
UV66-ADV-15-CAP-W-V2	15.6"	419,7	269	25	52	7
UV66-ADV-21-CAP-W-V2	21.5"	558,4	349,8	25	52	7

Montageausschnitt / Panel cut-out



	LCD	F (mm)	G (mm)	R (mm)
UV66-ADV-7-CAP-W-V2	7"	192,4	139	5
UV66-ADV-10-CAP-W-V2	10.1"	274,1	193,3	5
UV66-ADV-15-CAP-W-V2	15.6"	411,9	261,2	5
UV66-ADV-21-CAP-W-V2	21.5"	549,8	341,3	5

u-view ECO, BASIC and ADVANCED

